



Part Number : [190230008](#)
Product Description : InsulKrimp Fully Insulated Quick Disconnect, Male, for 12-10 AWG (5.00-3.30mm²) Wire, Tab 6.35 x 0.81mm, Bag
Series Number : 19023
Status : Active
Product Category : Quick Disconnects
Engineering Number : CMCT-2X



Documents & Resources

Drawings

[190230008_sd.pdf](#)

3D Models and Design Files

[190230008_stp.zip](#)

Specifications

[PS-19902-008-001.pdf](#)

[PS-19902-011-001.pdf](#)

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19023
Description	InsulKrimp Fully Insulated Quick Disconnect, Male, for 12-10 AWG (5.00-3.30mm ²) Wire, Tab 6.35 x 0.81mm, Bag
Comments	Funnel Entry
Product Name	InsulKrimp
Type	Quick Disconnect
UPC	800753039889

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Yellow
Flammability	94V-0
Gender	Male
Glow-Wire Capable	No

Insulated	Partial
Insulation	PVC
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Zinc Chromate
Material - Plating Termination	Zinc Chromate
Material - Resin	PVC
Net Weight	1.548/g
Orientation	Straight
Packaging Type	Bag
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-50° to +105°C
Wire Insulation Diameter	6.40mm max.
Wire Size (AWG)	10, 12

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Hand Crimp Tool InsulKrimp Male Q.D.	<u>640018100</u>
Air Powered Crimp Tool Head InsulKrimp Male Q.D.	<u>640058100</u>