



Part Number : [194390004](#)
Product Description : Loxon Locking Quick Disconnect, Female, for 14-16 Wire, Bag, Tab 6.35 x 0.81mm
Series Number : 19439
Status : Active
Product Category : Quick Disconnects
Engineering Number : BB-4151



Documents & Resources

Drawings
[194390004_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 34
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19439
Description	Loxon Locking Quick Disconnect, Female, for 14-16 Wire, Bag, Tab 6.35 x 0.81mm
Product Name	Loxon
Type	Quick Disconnect
UPC	193264611713

Agency

UL	E79133
----	--------

Electrical

Voltage - Maximum	600V AC
-------------------	---------

Physical

Barrel Type	Closed
Gender	Female
Glow-Wire Capable	No
Insulated	No
Insulation	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.835/g
Orientation	Straight
Packaging Type	Bag
Tab Thickness	0.81mm

Tab Width	6.35mm
Temperature Range - Operating	-40° to +149°C
Wire Insulation Diameter	3.15-3.60mm
Wire Size (AWG)	14, 16

Use with Part(s)

Description	Part Number
Loxon Locking Quick Disconnect Housing, Nylon, UL94V-2, Natural	<u>194390007</u>
Loxon Locking Quick Disconnect Housing, Nylon, UL94V-0, Natural	<u>194390008</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for Locking Quick Disconnect Crimp Terminals, 16-14 AWG	<u>2133094200</u>