



Part Number : [191980006](#)
Product Description : Avikrimp Spade Tongue
Terminal for 22-18 AWG Wire
Series Number : 19198
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : AA-835-10



Documents & Resources

Drawings
[191980006_sd.pdf](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19198
Description	Avikrimp Spade Tongue Terminal for 22-18 AWG Wire
Keyword	Spade Terminal, Spade Terminals
Product Name	Avikrimp
Type	Spade
UPC	800753045989

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Flammability	94V-0
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	0.787/g
Packaging Type	Bag
Stud Size	10 (M5)
Wire Insulation Diameter	3.60mm max.
Wire Size (AWG)	18, 20, 22
Wire Size mm ²	0.35-0.80

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 22-10 AWG and 6.0-0.5mm ² (Rings, Spades, Hooks, Block Spades and Flanged Spades)	<u>640010100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050100</u>
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	<u>640160036</u>