



Connectors > Connector Accessories > Connector Adapters & Connector Savers



Connector Interface Adapter Type: **Between Series Adapter**

Body Orientation: **Straight**

Side A Interface: **N Type**

Side A Gender: **Jack**

Side B Interface: **4.1/9.5**

Features

Product Type Features

Connector Interface Adapter Type	Between Series Adapter
Side A Interface	N Type
Side A Gender	Jack
Side B Interface	4.1/9.5
Side B Gender	Plug
Sealable	No

Configuration Features

Number of Positions	1
---------------------	---

Electrical Characteristics

Impedance	50 Ω
-----------	------

Housing Features

Body Orientation	Straight
------------------	----------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2016703-6
N M TO SMA M, 18G, 0.6M WITH ARMOR



TE Part # 2016658-6
N M DOUBLE, 18G, 0.6M WITH ARMOR, PUR



TE Part # 2016657-6
N M DOUBLE, 18G, 0.6M WITHOUT ARMOR



TE Part # 1-2016703-5
N M TO SMA M, 18G, 1.5M WITH ARMOR





TE Part # 1-2016703-0
N M TO SMA M, 18G, 1.0M WITH ARMOR



TE Part # 1-2016658-0
N M DOUBLE, 18G, 1.0M WITH ARMOR, PUR



TE Part # 1-2016658-5
N M DOUBLE, 18G, 1.5M WITH ARMOR, PUR



TE Part # 2081557-1
ADAPTOR N MALE TO 7-16 MALE



TE Part # 1-2016657-5
N M DOUBLE, 18G, 1.5M WITHOUT ARMOR



TE Part # 1-2016657-0
N M DOUBLE, 18G, 1.0M WITHOUT ARMOR

Customers Also Bought



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT



TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



TE Part #DT04-2P
REC, 2P, GRY, N




TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts



TE Part #DT06-2S
PLG, 2P, GRY, N



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING



TE Part #281934-2
SINGLE WIRE SEAL

Documents

- Product Drawings

ADAPTOR 4.1-9.5 PLUG TO N JACK

English
- CAD Files

3D PDF

3D
- Customer View Model

ENG_CVM_CVM_2081553-1_A.2d_dxf.zip

2081553-1

Between Series Adapter, Straight, N Type Side A, Jack Side A, 4.1/9.5 Side B, Plug Side B, 1 Position



English

Customer View Model

[ENG_CVM_CVM_2081553-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2081553-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English