



(Intenso)[®]
for everyday life



POWERBANK

F10000 + F20000 | 20 W

Mobiler Zusatzakku

(Intenso)[®]
for everyday life

QUALITÄTSPRÜFUNG
In Deutschland getestet ✓

Technische Informationen

Akku:	10000 mAh, 20000 mAh
Farben:	Lila, Grau, Blau + Grün (10000 + 20000 mAh), Orange + Gelb (10000 mAh)
Batterietyp:	Lithium-Polymer Akku
Anschlüsse:	Output USB-A: 5,0 V/DC 3,0 A USB-A QC: 5,0 V/DC 3,0 A, 9,0 V/DC 2,0 A, 12,0 V/DC 1,5 A (max. 18,0 W) USB-C Out: 5,0 V/DC 3,0 A USB-C PD Out: 5,0 V/DC 3,0 A, 9,0 V/DC 2,22 A, 12,0 V/DC 1,67 A PPS: 5,0 – 5,9 V/DC 3,0 A 5,0 – 11,0 V/DC 2,0 A (max. 20,0 W) USB-A + USB-C Out: 5,0 V/DC 3,0 A gesamt Input USB-C In: 5,0 V/DC 3,0 A USB-C PD In: 5,0 V/DC 3,0 A, 9,0 V/DC 2,0 A (max. 18,0 W)
Anzeige:	Digitale Prozentanzeige
Eigenschaften:	Überspannungsschutz, Entladeschutz, Überladeschutz, Kurzschlusssicherung
Zubehör:	USB-C zu USB-C Ladekabel (unterstützt Power Delivery), Schlaufe
Abmessungen + Gewicht:	F10000: 131 x 67 x 15 mm, 222 g F20000: 131 x 67 x 28 mm, 365 g
VPE:	2 Stück

Artikeldaten

Kapazität + Farbe	Art.-Nr.	EAN
10000 mAh, Lila	7332033	4 034303 034284
10000 mAh, Grau	7332034	4 034303 034192
10000 mAh, Blau	7332035	4 034303 034222
10000 mAh, Grün	7332037	4 034303 034253
10000 mAh, Orange	7332038	4 034303 034314
10000 mAh, Gelb	7332039	4 034303 034345
20000 mAh, Lila	7332053	4 034303 036066
20000 mAh, Grau	7332054	4 034303 034765
20000 mAh, Blau	7332055	4 034303 034796
20000 mAh, Grün	7332057	4 034303 034826



PD Extra schnelles Laden mit
Power Delivery 3.0 (20 W)

* Für Details besuchen Sie bitte die folgende Webseite:
<https://www.qualcomm.com/products/snapdragon/quick-charge>

Qualcomm® Quick Charge™ is a product of Qualcomm Technologies, Inc. Qualcomm is a trademark of Qualcomm Incorporated, registered in the United States and other countries. Quick Charge is a trademark of Qualcomm Incorporated. All Qualcomm Incorporated marks are used with permission.