ALL-IN-ONE PCS

Modern AM242P 1M

MODERN AM242P 1M-1873AT


Be Your Window To The World

Der MSI Modern Series All-in-One PC ist nicht mehr nur ein funktionales Produkt, das sich ausschließlich auf die Erfüllung der Anforderungen der Benutzer konzentriert, sondern er repräsentiert den handwerklichen Geist der Exzellenz und die uneingeschränkte Freiheit der modischen Einstellung. Auch die Modern Series verfügt über Funktionen, die den Bedürfnissen der Benutzer voll und ganz gerecht werden, und ein Aussehen, das sich in verschiedene Umgebungen integrieren lässt. Egal, wo Sie sind, Sie müssen Ihren Stil und Ihre Ausdauer im Leben bewahren.



SELLING POINTS

- Windows 11 Home - MSI empfiehlt Windows 11 Pro für Unternehmen
- 27 Zoll IPS-Grade Panel LED Backlight (1920 x 1080 FHD) mit TÜV zertifizierten Anti-Flicker und Less Blue Light Technologien
- Intel® Core™ 3 Prozessor 100U mit DDR5 Arbeitsspeicher
- 24/7 Qualified Reliability Test
- Der verstellbare Standfuß bietet eine bequeme Arbeitsumgebung
- Durch die MSI Instant-Display-Technologie lässt sich das Gerät als Monitor verwenden, ohne dafür das System hochfahren zu müssen
- dTPM und die integrierte FHD-Webcam mit Windows Hello verbessern die Privatsphäre der Benutzer und schützen vertrauliche Daten
- MSI Storage Rapid Upgrade Design erleichtert die schnelle Aufrüstung oder Wartung von 2,5"-Datenträger
- MSI Cloud Center ermöglicht es Benutzern, eine private Cloud zu erstellen und Dateien von Android- und iOS-Geräten zu sichern
- Die MSI AI Engine erkennt automatisch Benutzerszenarien und passt Leistung, Soundeffekte und Anzeigemodus entsprechend an



1. 2x USB3.2 Gen 2 Typ C
2. 2x USB3.2 Gen 2 Typ A
3. 1x Mikrofon-Eingang/Kopfhörer-Ausgang Kombo
4. 1x 2.5” Schacht
5. 5-Wege Navigation
6. 1x Stromanschluss
7. 1x Kensington Lock
8. 1x HDMI™ in
9. 1x HDMI™ out (unterstützt 4K @60Hz nach HDMI™ 2.1)
10. 2x USB 2.0 Typ A
11. 1x RJ45 LAN
12. 1x Abnehmbare Webcam-Abdeckung

“2025-06-12 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products.”

ALL-IN-ONE PCS

Modern AM242P 1M

MODERN AM242P 1M-1873AT

SPECIFICATION

Betriebssystem	OS	MULTI-LANGUAGE(WIN 11 HOME PLUS OLC OA3)
	Operating Systems	Windows 11 Home
Model	MKT SKU	00AE0722-1873
	MKT Spec	Modern AM242P 1M-1873AT
	Color	ID1/White-White-White
Chipsatz	Chipsets	SoC
Arbeitsspeicher	Memory Size	16GB(8GB*2)
	Memory Type	DDR5 SDRAM
	Memory Speed	2800(5600)MHz
	Module Type	SO-DIMM
	Memory Slot(Total)	2
	Memory Slot(Free)	0
	Max Capacity	Max 64GB
Prozessor	CPU Number	Intel Core 3 Processor 100U
	CPU Clock	1.2GHz
	CPU Cores	6
	TDP	15W
	Max Turbo Frequency	up to 4.70 GHz
	Cache	10 MB Intel® Smart Cache
	Threads	8
Display	View Angles	178°(H)/178°(V)
	Touch Screen	Non-touch
	Screen Size	23.8" (60cm)
	Panel Type	IPS
	Resolution	1920x1080 (FHD)
	Brightness (nits)	250
	Contrast Ratio	1000:1
	Refresh Rate	N/A
	Response Time (GTG)	14ms
Grafik	GPU1 Vendor	N/A
	GPU1 MKT Name	N/A
	GPU1 Number	UMA
	GPU1 VRAM Size	N/A
	GPU1 VRAM Type	N/A
Audio	Audio Chipset	Realtek ALC256
	Audio Type	2.1 Channel HD Audio
Speicher	SSD Interface	PCIe GEN4x4
	SSD Form Factor	M.2-2280 M-KEY
	SSD Config	256GB*1
	SSD Size	256GB
	HDD1 Interface	N/A
	HDD1 Form Factor	N/A
	HDD1 Size	N/A
	HDD1 RPM	N/A
	ODD(Type)	N/A
	ODD Height	N/A
	ODD Type	N/A
	mSATA slots(Free)	0
	M.2 slots(Total)	1
	M.2 slots(Free)	0
	2.5" Drive Bays(Total)	1
	2.5" Drive Bays (Free)	1
	3.5" Drive Bays(Free)	0
Kommunikation	LAN	Realtek RTL8111H
	WLAN Version	Wi-Fi 6E+BT
	BT Version	5.3
Input Device	Webcam	internal webcam
	Webcam Resolution	N/A
	Webcam supports Windows Hello or not	Yes

"2025-06-12 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."

ALL-IN-ONE PCS

Modern AM242P 1M

MODERN AM242P 1M-1873AT

Schnittstellen (Seite)	Mic-in/Headphone-out combo	1
	USB 3.2 Gen 2 (10G) Type C	2
	USB 3.2 Gen 2 (10G) Type A	2
Schnittstellen (Rückseite)	USB 2.0 Type A (R)	2
	RJ45	1
	HDMI out	1x (v2.1)
	HDMI in	1
	Lock type	Kensington
Garantie	Warranty	24 Monate Pick-Up & Return
Abmessungen & Gewicht	Product Dimension with Holder (WxDxH) (mm)	N/A
	Product Dimension with Holder (WxDxH) (inch)	N/A
	Product Dimension with Stand (WxDxH) (mm)	N/A
	Product Dimension with Stand (WxDxH) (inch)	N/A
	Outer Carton Dimension with Holder (WxDxH) (mm)	N/A
	Outer Carton Dimension with Holder (WxDxH) (inch)	N/A
	Outer Carton Dimension with Stand (WxDxH) (mm)	652 x 222 x 455
	Outer Carton Dimension with Stand (WxDxH) (inch)	25.67 x 8.74 x 17.91
	Weight (Net kg)	N/A
	Weight (Net lbs)	N/A
	Weight (Gross kg)	N/A
	Weight (Gross lbs)	N/A
STAND	Adjustment (Tilt)	-5°~20° ±2°
	Adjustment (Swivel)	N/A
	Adjustment (Height)	0~130mm
	Adjustment (Pivot)	N/A
Power	AC Adapter Output	120W
VESA	VESA size	75 x 75 mm
Lagerung & Zertifikationen	Regulatory Compliance	FCC(Class B), CB/CE, UL(CUL), BSMI, VCCI, RCM(C-Tick)
Zubehör	AC Adaptor	1
	Power Cord	1
	Warranty Card	N/A
	Quick Guide	4
	User Manual	N/A
	VESA Mount kit	N/A
	Keyboard Interface	USB
	Mouse	SM9023MW
	Mouse Interface	USB
Barcode Info	EAN	4711377339803

“2025-06-12 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products.”