

Dreame X50 Ultra 0,395 l Kombi Edelstahl, Weiß

Marke : Dreame Artikel-Code: 6977328065025
Produktname : X50 Ultra

Dreame X50 Ultra. Staubbehälter Typ: Kombi, Produktfarbe: Edelstahl, Weiß, Form: Rund. Staubkapazität (gesamt): 0,395 l, Geräuschpegel: 70 dB, Fassungsvermögen Wassertank: 4,5 l. Akku-/Batteriekapazität: 6400 mAh, Laufzeit: 220 min, Batterielebensdauer: 205 m². Höhe: 111 mm, Breite: 350 mm, Tiefe: 350 mm. Verpackungsbreite: 419 mm, Verpackungstiefe: 519 mm, Verpackungshöhe: 691 mm



Design		Energie	
Staubbehälter Typ *	Kombi	Laufzeit *	220 min
Produktfarbe *	Edelstahl, Weiß	Batterielebensdauer	205 m²
Form	Rund	Gewicht und Abmessungen	
Leistungen		Höhe	111 mm
Nasswischen *	✓	Breite	350 mm
Staubkapazität (gesamt) *	0,395 l	Tiefe	350 mm
Fassungsvermögen Wassertank	4,5 l	Gewicht	4,53 kg
Stabsauger-Programme	Teppich, Intensiv	Basisstation Abmessungen (B x T x H)	340 x 457 x 590 mm
Selbstentleerer Staubbehälter	✓	Gewicht Basisstation	9,09 kg
Automatische Rückkehr zur Basisstation *	✓	Verpackungsdaten	
Hinderniserkennung	✓	Verpackungsbreite	419 mm
Material Bürste	Gummi	Verpackungstiefe	519 mm
Anzahl der Bürsten	2	Verpackungshöhe	691 mm
Bürstentyp	Walzenbürste & Seitenbürste	Paketgewicht	19,6 kg
unterstützte Bodenflächen	Teppich, Harter Boden	Lieferumfang	
Schwellensteigerung (max)	6 cm	Benutzerhandbuch	✓
Navigationstyp	3D Smart Navigation, Mapping	Betriebsanleitung	✓
Geräuschpegel *	70 dB	Basisstation	✓
Funktioniert mit Amazon Alexa	✓	Technische Details	
Einfach zu säubern	✓	Reinigungsbürste	✓
Energie		Anzeigelicht	✓
Akku-/Batteriekapazität *	6400 mAh		

Technische Details

Saugleistung	20000 Pascal
Kompatible Produkte	Apple Watch
Kompatibilität	TUV



6977328065025

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.