


Samsung 990 Pro 4 TB M.2 PCI Express 4.0 NVMe V-NAND TLC

Marke : Samsung

Artikel-Code: MZ-V9P4T0CW

Produktname : 990 Pro



- PCIe® 4.0 NVMe™ SSD für High-End-Gaming für Konsole und PC
 - Langanhaltende Leistung dank effizientem Kühlkörper
 - Hohe Lesegeschwindigkeit von bis zu 7.450 MB/s und Schreibgeschwindigkeit von bis zu 6.900 MB/s
 - 50 % verbesserte Leistung pro Watt gegenüber der 980 PRO Heatsink
 - Unterstützt Direct Storage bei Windows 11
 - Das integrierte RGB-Licht lässt sich mit der Magician Software individuell anpassen
- 990 PRO Heatsink NVMe™ M.2 SSD - 4 TB
- Samsung 990 Pro. SSD Speicherkapazität: 4 TB, SSD-Formfaktor: M.2, Lesegeschwindigkeit: 7450 MB/s, Schreibgeschwindigkeit: 6900 MB/s, Komponente für: PC/Spielekonsole

Merkmale		Energie	
NVMe Version	2.0	Arbeitsspannung	3,3 V
Unterstützte Sicherheitsalgorithmen	256-bit AES	Stromverbrauch (max.)	7,8 W
SSD Speicherkapazität *	4 TB	Stromverbrauch (durchschnittl.)	5,4 W
SSD-Formfaktor *	M.2	Gewicht und Abmessungen	
Schnittstelle *	PCI Express 4.0	Breite	25 mm
NVMe *	✓	Tiefe	80,2 mm
Speichertyp *	V-NAND TLC	Höhe	8,88 mm
Komponente für *	PC/Spielekonsole	Gewicht	28 g
Hardwareverschlüsselung *	✓	Verpackungsdaten	
M.2 SSD- Größe	2280 (22 x 80 mm)	Verpackungsart	Karton mit Aufhänger
Lesegeschwindigkeit	7450 MB/s	Betriebsbedingungen	
Schreibgeschwindigkeit	6900 MB/s	Betriebstemperatur	0 - 70 °C
S.M.A.R.T. Unterstützung	✓	Stoßfestigkeit in Betrieb	1500 G
TRIM-Unterstützung	✓	Sonstige Funktionen	
Mittlere Betriebsdauer zwischen Ausfällen (MTBF)	1500000 h	Garantiezeit	5 Jahr(e)



8806094946857

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.