

Produktdatenblatt

Product Data Sheet

Universal-Dimmer Weiß LED 3-250W / Halogen 3-400W



Basis Daten

Base Data

Artikelnummer <i>Articlenumber</i>	DM001
Hersteller <i>Manufacturer</i>	LEDmaxx
Marke <i>Brand</i>	LEDmaxx
Farbe <i>Colour</i>	Weiß <i>White</i>

Produkt Daten

Product Data

Leistung LED in W <i>LED power in W</i>	3 - 250
Leistung Halogen in W <i>Halogen power in W</i>	3 - 400
Dimmart <i>Dimming type</i>	Phasenabschnitt-Dimmer <i>Phase-cut dimmer</i>
Betriebstemperaturbereich <i>Operating temperatur range</i>	5 - 25
Stromstärke in VA <i>Amperage in VA</i>	3 - 400
Frequenz in Hz <i>Frequency in Hz</i>	50/60
Spannung in V <i>Voltage in V</i>	220 - 240 AC

Abmessungen und Gewicht

Dimension and Weight

Breite in mm <i>Width in mm</i>	84
Länge in mm <i>Length in mm</i>	84
Einbauhöhe in mm <i>Installation height in mm</i>	25.7
Gesamthöhe in mm <i>Total height in mm</i>	37.2
Nettogewicht in g <i>Net. Weight in g</i>	90

Bestellungen und Verpackungsinformation

Ordering and Packaging Information

Artikelnummer <i>Article number</i>	EAN <i>Barcode</i>	Stück <i>Pieces</i>	Abmessungen <i>Dimension (in mm)</i>	Gewicht <i>Weight gross (in g)</i>	Volumen <i>Volume (in dm³)</i>
DM001	4251351808418	1	88 x 88 x 70	120	0.54
DM001	4251351808418	100	480 x 480 x 300	12500	69.12