

							
Artikelnummer (Farbe Grau)	DN-97609	DN-97610	DN-97614	DN-19 TRAY-2-55		DN-10 TRAY-1	DN-10-TRAY-2
Artikelnummer (Farbe Schwarz)	DN-19 TRAY-1-SW	DN-19 TRAY-2-SW	DN-19 TRAY-1-400-SW	DN-19 TRAY-2-55-SW	DN-19 TRAY1-1000-ECB	DN-10-TRAY-1-B	DN-10-TRAY-2-B
Geeigneter Schranktyp	19 Zoll	19 Zoll	19 Zoll	19 Zoll	19 Zoll	10 Zoll	10 Zoll
Geeignete Schranktiefe	alle	≥ 450 mm	≥ 600 mm	≥ 800 mm	≥ 1000 mm	alle	alle
Abmessungen (H x B x T)	45 x 483 x 250 mm	88 x 482 x 349 mm	44 x 482 x 399 mm	88 x 482 x 549 mm	44 x 486 x 770 mm	44 x 254 x 150 mm	44 x 254 x 200 mm
Höheneinheiten (U)	1U	2U	1U	2U	1U	1U	1U
Traglast	15 kg	25 kg	15 kg	25 kg	50 kg	25 kg	25 kg
Einbautyp	Festeinbau	Festeinbau	Festeinbau	Festeinbau	Festeinbau	Festeinbau	Festeinbau
Befestigung auf 19"/10" Profilen	2-Punkt-Befestigung	2-Punkt-Befestigung	2-Punkt-Befestigung	2-Punkt-Befestigung	4-Punkt-Befestigung	2-Punkt-Befestigung	2-Punkt-Befestigung