

1

2

3

www.testo.com/manuals

Ø 145 mm / 5.71 in Cable 1,45 m / 57.1 in	0 ... +120 °C +32 ... +248 °F	Type K thermocouple, class 1	0,01 °C 0.01 °F	≈ 30 min