

Datasheet | Teppanyaki Table Grill

Baking surface (l x w): 47.5 x 26.5 cm | 5 Heat Settings

Brand: Nedis | Article number: FCTE110EBK50 | Product EAN number: 5412810268344

Product specifications

Baking surface (l x w)	47.5 x 26.5 cm
Colour	Black
Indicator light	Yes
Input voltage	230 V AC 50 Hz
Material	Metal
Maximum power consumption	2000 W
Number of heat settings	5 Heat Settings
Number of products in package	1 pcs
Power	2000 W
Power cable length	0.90 m
Power plug	Type F (CEE 7/7)
Power source type	Mains Powered
Removable fat collector	Yes
Size	585 mm (L) x 280 mm (W) x 105 mm (H)
SmartLife	No

Packaging information

Brand	Nedis
Order code	FCTE110EBK50
EAN single product:	5412810268344
EAN Inner carton:	
EAN Outer carton:	5412810371457
Packaging	Giftbox
Package contents	Griddle
	Grease drip tray

Quantity	L x	W x	H (mm)	Weight
1	125 mm	285 mm	610 mm	2260 g
4	310 mm	520 mm	630 mm	9800 g

