



Datasheet | Teppanyaki Table Grill

Baking surface (l x w): 90 x 23 cm | 5 Heat Settings

Brand: Nedis | Article number: FCTE110EBK90 | Product EAN number: 5412810268351

Product specifications

Baking surface (l x w)	90 x 23 cm
Colour	Black
Indicator light	Yes
Input voltage	230 V AC 50 Hz
Material	Metal
Maximum power consumption	1800 W
Number of heat settings	5 Heat Settings
Number of products in package	1 pcs
Power	1800 W
Power cable length	0.90 m
Power plug	Type F (CEE 7/7)
Power source type	Mains Powered
Removable fat collector	Yes
Size	1025 mm (L) x 260 mm (W) x 105 mm (H)
SmartLife	No

Packaging information

Brand	Nedis
Order code	FCTE110EBK90
EAN single product:	5412810268351
EAN Inner carton:	
EAN Outer carton:	5412810371464
Packaging	Giftbox
Package contents	Griddle
	Grease drip tray

Quantity	L x	W x	H (mm)	Weight
1	125 mm	260 mm	1040 mm	346 g
3	285 mm	400 mm	1060 mm	11150 g

