

## 2 Bread Slices | 2 Slots | Browning levels: 6 | Black

Brand: Nedis | Article number: KABT150EBK | Product EAN number: 5412810334346

### Product specifications

|                               |                                  |
|-------------------------------|----------------------------------|
| Browning levels               | <b>6</b>                         |
| Colour                        | <b>Black</b>                     |
| Cord storage space            | <b>Yes</b>                       |
| Defrost feature               | <b>No</b>                        |
| Eject button                  | <b>No</b>                        |
| Indicator light               | <b>No</b>                        |
| Input voltage                 | <b>220 - 240 V AC 50/60 Hz</b>   |
| Material                      | <b>Plastic</b>                   |
| Maximum power consumption     | <b>700 W</b>                     |
| Non-slip feet                 | <b>Yes</b>                       |
| Number of bread slices        | <b>2 Bread Slices</b>            |
| Number of products in package | <b>1 pcs</b>                     |
| Number of slots               | <b>2 Slots</b>                   |
| Power cable length            | <b>0.70 m</b>                    |
| Power plug                    | <b>French / Type E (CEE 7/6)</b> |
| Power source type             | <b>Mains Powered</b>             |
| Removable crumb tray          | <b>Yes</b>                       |
| SmartLife                     | <b>No</b>                        |
| Toast clamp                   | <b>No</b>                        |

### Packaging information

|                     |                      |
|---------------------|----------------------|
| Brand               | <b>Nedis</b>         |
| Order code          | <b>KABT150EBK</b>    |
| EAN single product: | <b>5412810334346</b> |
| EAN Inner carton:   |                      |
| EAN Outer carton:   | <b>5412810371570</b> |
| Packaging           | <b>Box</b>           |
| Package contents    | <b>1x toaster</b>    |
|                     | <b>manual</b>        |

| Quantity | L x    | W x    | H (mm) | Weight |
|----------|--------|--------|--------|--------|
| 1        | 155 mm | 175 mm | 270 mm | 874 g  |
| 6        | 285 mm | 370 mm | 465 mm | 5760 g |

