



Datasheet | Electric Kettle

1.8 l | Soft-Touch | Grey | Rotatable 360 degrees | Concealed heating element | Strix® controller | Boil-dry protection

Brand: Nedis | Article number: KAWK520EGY | Product EAN number: 5412810273768

Product specifications

Anti slip bottom	Yes
Boil-dry protection	Yes
Capacity	1.8 l
Colour	Grey
Concealed heating element	Yes
Cord storage space	Yes
Housing material	Soft-Touch
Indicator light	Yes
Input voltage	220 - 240 V AC 50/60 Hz
Limescale filter	Yes
Material	Stainless Steel
Maximum power consumption	2200 W
Number of products in package	1 pcs
Power cable length	0.70 m
Power plug	Type F (CEE 7/7)
Power source type	Mains Powered
Rotatable 360 degrees	Yes
Shape water cooker	Kettle-shape
SmartLife	No
Strix® controller	Yes
Warning signal	No
Water level indicator	Yes

Packaging information

Brand	Nedis
Order code	KAWK520EGY
EAN single product:	5412810273768
EAN Inner carton:	
EAN Outer carton:	5412810372201
Packaging	Giftbox
Package contents	Electric kettle
	Manual

Quantity	L x	W x	H (mm)	Weight
1	250 mm	290 mm	270 mm	1640 g
4	515 mm	320 mm	555 mm	7520 g

