BUSINESS & PRODUCTIVITY PCS

Cubi NUC AI 1UMG

CUBI NUC AI 1UMG-073AT

Be Your Window To The World


reddot winner 2024



Picture and logos

SELLING POINTS

- Windows 11 Home – MSI empfiehlt Windows 11 Pro für Unternehmen
- 0,51-Liter-Design mit VESA-Montageoption
- Bis zu Intel® Core™ Ultra 7 Prozessor 155H mit Intel® Boost NPU
- Dual-Channel DDR5 SO-DIMM-Arbeitsspeicher
- Zwei Thunderbolt™ 4 & Dual 2.5G LAN & dTPM-Unterstützung
- Unterstützung für vier Displays & leicht aufrüstbares Design
- MSI Power Link: Cubi NUC kann über MSI Power Link-Technologie vom Monitor mit Strom versorgt werden
- MSI AI Engine: Optimiert das Nutzungserlebnis ohne manuelle Konfiguration
- Power Meter ermöglicht Energieeinsparung per Klick, CO_2-Berechnung und Abschätzung der Stromkosten
- Hergestellt aus PCR-recyceltem Kunststoff; FSC™-zertifizierter Karton; Abfallreduzierung durch recycelte Formmasse (100 % recycelbar); Produziert mit 99 % erneuerbarer Energie im Werk



1. 1x USB 10Gbps Typ A
2. 1x USB 10Gbps Typ A
3. 1x USB 10Gbps Typ C
4. 1x Kensington Lock
5. 1x Exterer Power Switch Anschluss
6. 1x Stromanschluss
7. 1x HDMI Ausgang (unterstützt 4K @60Hz nach HDMI 2.1) welcher MSI Power Link unterstützt
8. 2x RJ45 LAN (2.5G)
9. 1x HDMI Ausgang (unterstützt 4K @60Hz nach HDMI 2.1)
10. 1x Thunderbolt 4 (DP 1.4 alt-mode bis zu 4K@60Hz / PD-out 15W)
11. 1x Thunderbolt 4 (DP 1.4 alt-mode bis zu 4K@60Hz / PD-out 15W)

"2026-06-12 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."

BUSINESS & PRODUCTIVITY PCS

Cubi NUC AI 1UMG

CUBI NUC AI 1UMG-073AT

SPECIFICATION

Betriebssystem	Betriebssystem	Windows 11 Pro
Prozessor	CPU Number	Intel Core Ultra 5 processor 125H
	CPU Clock	1.2GHz
	CPU Cores	14
	TDP	28W
	Cache	18 MB Intel® Smart Cache
	Threads	18
	Max Turbo Frequency	up to 4.50 GHz
	CPU Cooler	Air cooling
	Platform TOPS	Up to 36
	NPU TOPS	Up to 11
Chipsatz	Chipsets	Soc
Grafik	GPU1 VRAM Size	N/A
	VGA I/O Port	N/A
	GPU1 Vendor	N/A
	GPU1 MKT Name	N/A
Arbeitsspeicher	Memory Size	16GB(16GB*1)
	Memory Type	DDR5 SDRAM
	Module Type	SO-DIMM
	Memory Slot (Total/Free)	2/1
	Max Capacity	Max 64GB
Speicher	SSD Interface	PCIe GEN4x4
	SSD Form Factor	M.2-2280 M-KEY
	SSD Config	512GB*1
	SSD Size	512GB
	HDD1 Interface	N/A
	HDD1 Form Factor	N/A
	HDD1 Size	N/A
	HDD1 RPM	N/A
	ODD(Type)	N/A
	ODD Height	N/A
	ODD Type	N/A
	M.2 slots (Total/Free)	2/1
	2.5" Drive Bays (Total/Free)	0/
	3.5" Drive Bays (Total/Free)	0/
Kommunikation	LAN	2x Intel I226-V
	WLAN Version	Wi-Fi 6E+BT
	BT Version	5.3
	WLAN	INTEL/AX211.NGWG.NV
Schnittstellen (Vorne)	USB 3.2 Gen 2 (10G) Type C	1
	USB 3.2 Gen 2 (10G) Type A	2
	Copilot Button	1
Schnittstellen (Rückseite)	Thunderbolt (R)	2x (Thunderbolt 4)
	RJ45	2
	HDMI out	2x (HDMI v2.1 Support up to 4K@60Hz)
	Lock type	Kensington Lock
Power	Power	120W
	Power Certification	N/A
	Formfactor	N/A
	Type	ADAPTOR
VESA	VESA size	100 x 100 mm

"2026-06-12 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."

BUSINESS & PRODUCTIVITY PCS

Cubi NUC AI 1UMG

CUBI NUC AI 1UMG-073AT

Abmessungen & Gewicht	Product Dimension (WxDxH) (mm)	119.6 x 115.2 x 37.5
	Product Dimension (WxDxH) (inch)	4.71 x 4.54 x 1.48
	Inside Carton Dimension (WxDxH) (mm)	205 x 220 x 94
	Inside Carton Dimension (WxDxH) (inch)	8.07 x 8.66 x 3.7
	Outer Carton Dimension Standard (WxDxH) (mm)	N/A
	Outer Carton Dimension Standard (WxDxH) (inch)	N/A
	Weight (Net kg)	0.55
	Net Weight (lbs)	1.21
	Weight (Gross kg)	1.24
	Gross Weight (lbs)	2.73
	Liter	N/A
	Pint	N/A
Lagerung & Zertifikationen	Operating, Storage Temperature	0° C ~ 35° C ; -20° C ~ 60° C
	Operating, Storage Humidity	0% ~ 85%;0% ~ 90%
	Regulatory Compliance	BSMI, CB/CE, FCC(Class B), UL(CUL), VCCI
Garantie	Warranty	36months
Zubehör	Keyboard Interface	N/A
	Mouse Interface	N/A
	Power Cord	1
	AC Adaptor	1
	Warranty Card	N/A
	Quick Guide	3
	User Manual	N/A
	VESA Mount kit	1
	Keyboard	N/A
	Mouse	N/A
	Power Switch	N/A
Barcode Info	EAN	4711377424639
Model	Part No	9S6-B20911-073
	MKT Name	Cubi NUC AI 1UMG
	MKT Spec	Cubi NUC AI 1UMG-073AT
	Color	ID1/Black-Black-Black
	Model	B209
Security	TPM module	N/A
	Chassis Lock	N/A
	Chassis Intrusion	N/A

“2026-06-12 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products.”