BUSINESS & PRODUCTIVITY PCS

# PRO DP10 A14MG

PRO DP10 A14MG-018AT


## PATH TO THE FUTURE



Picture and logos

## SELLING POINTS

- Windows 11 HomeMSI empfiehlt Windows 11 Pro für Unternehmen
- 1,1 Liter mit VESA-montierbarem Design
- Bis zu Intel® Core™ i7 Prozessor 14700
- Dual-Channel-DDR5-SO-DIMM-Speicher
- 8x USB Typ A, 1x USB Typ C, Dual-2,5G-LAN (mit konfigurierbarem Port)
- Unterstützung für drei Displays
- MSI Power Link: Das PRO DP10 A14MG kann über die MSI Power Link-Technik vom Monitor mit Strom versorgt werden
- MSI AI Engine: Optimiere das Benutzererlebnis ohne manuelle Konfiguration.
- Power Meter ermöglicht Energiesparen mit einem Klick, die Berechnung der $CO_2$-Emissionen und die Schätzung der Stromkosten
- Ausgestattet mit FSC™-zertifiziertem Karton; Abfallreduzierung durch recycelte Formmasse (100 % recycelbar); Hergestellt mit 99 % erneuerbarer Energie im Werk




1. 1x USB 2.0
2. 2x USB 5Gb Type A
3. 1x USB 10Gb Type A
4. 1x USB 10Gb Type C
5. 1x Mic-in/Headphone-out combo
6. 1x External Power Switch Pin Header
7. 1x DC Jack
8. 1x HDMI out (supports 4K @60Hz as specified in HDMI 2.1) which supports the MSI Power Link
9. 1x DisplayPort 1.4b (supports 4K@60Hz)
10. 4x USB 2.0
11. 1x LAN port (2.5G)
12. 1x Configurable Port (Default: HDMI+LAN(2.5G); Optional for HDMI+COM/ DP+LAN(2.5G)/ DP+COM/ VGA+LAN(2.5G)/ VGA+COM)
13. 1x Kensington Lock
14. 1x WiFi Antenna

"2026-05-23 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."

BUSINESS & PRODUCTIVITY PCS

# PRO DP10 A14MG

PRO DP10 A14MG-018AT

## SPECIFICATION

| | | |
|---|---|---|
| Betriebssystem | Betriebssystem | Windows 11 Pro |
| Prozessor | CPU Number | Intel Core i7 Processor 14700 |
| | CPU Clock | 2.1GHz |
| | CPU Cores | 20 |
| | TDP | 65W |
| | Cache | 33 MB Intel® Smart Cache |
| | Threads | 28 |
| | Max Turbo Frequency | up to 5.40 GHz |
| | CPU Cooler | Air cooling |
| | Platform TOPS | N/A |
| | NPU TOPS | N/A |
| Chipsatz | Chipsets | H610 |
| Grafik | GPU1 VRAM Size | N/A |
| | VGA I/O Port | N/A |
| | GPU1 Vendor | N/A |
| | GPU1 MKT Name | N/A |
| Arbeitsspeicher | Memory Size | 16GB(8GB*2) |
| | Memory Type | DDR5 SDRAM |
| | Module Type | SO-DIMM |
| | Memory Slot (Total/Free) | 2/0 |
| | Max Capacity | Max 64GB |
| Speicher | SSD Interface | PCIe GEN4x4 NVMe |
| | SSD Form Factor | M.2 2280 M-KEY |
| | SSD Config | 512GB*1 |
| | SSD Size | 512GB |
| | HDD1 Interface | N/A |
| | HDD1 Form Factor | N/A |
| | HDD1 Size | N/A |
| | HDD1 RPM | N/A |
| | ODD(Type) | N/A |
| | ODD Height | N/A |
| | ODD Type | N/A |
| | M.2 slots (Total/Free) | 1/0 |
| | 2.5" Drive Bays (Total/Free) | 0/ |
| | 3.5" Drive Bays (Total/Free) | 0/ |
| Audio | Audio Chipset | Realtek ALC256 |
| | Audio Type | 2-Channel High Definition Audio |
| Kommunikation | LAN | 2x Intel I226-V |
| | WLAN Version | Wi-Fi 6E+BT |
| | BT Version | 5.3 |
| | WLAN | INTEL/AX211.NGWG.NV |
| Schnittstellen (Vorne) | USB 2.0 Type A | 1 |
| | Mic-in/Headphone-out combo | 1 |
| | USB 3.2 Gen 2 (10G) Type C | 1 |
| | USB 3.2 Gen 2 (10G) Type A | 1 |
| | USB 3.2 Gen 1 (5G) Type A | 2 |
| Schnittstellen (Rückseite) | USB 2.0 Type A (R) | 4 |
| | RJ45 | 1 |
| | WiFi Antenna | 1 |
| | HDMI out | 1x (v2.1) |
| | DP out | 1x (v1.4) |
| | Lock type | Kensington Lock |
| | Configurable port | DP+COM, DP+LAN, HDMI+COM, HDMI+LAN, NA, VGA+COM, VGA+LAN |
| Power | Power | 120W |
| | Power Certification | N/A |
| | Formfactor | N/A |
| | Type | ADAPTOR |
| VESA | VESA size | 75 x 75 mm |

"2026-05-23 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."

BUSINESS & PRODUCTIVITY PCS

# PRO DP10 A14MG

PRO DP10 A14MG-018AT

| | | |
|---|---|---|
| Abmessungen & Gewicht | Product Dimension (WxDxH) (mm) | 178.82 x 34.48 x 179 |
| | Product Dimension (WxDxH) (inch) | 7.04 x 1.36 x 7.05 |
| | Inside Carton Dimension (WxDxH) (mm) | 249 x 102 x 306 |
| | Inside Carton Dimension (WxDxH) (inch) | 9.8 x 4.02 x 12.05 |
| | Outer Carton Dimension Standard (WxDxH) (mm) | 531 x 325 x 530 |
| | Outer Carton Dimension Standard (WxDxH) (inch) | 20.91 x 12.8 x 20.87 |
| | Weight (Net kg) | 1.225 |
| | Net Weight (lbs) | 2.7 |
| | Weight (Gross kg) | 2.44 |
| | Gross Weight (lbs) | 5.38 |
| | Liter | 1.1 |
| | Pint | 2.32 |
| Lagerung & Zertifikationen | Operating, Storage Temperature | 0° C ~ 35° C ; -20° C ~ 60° C |
| | Operating, Storage Humidity | 0% ~ 85%;0% ~ 90% |
| | Regulatory Compliance | BSMI, CB/CE, FCC(Class B), RCM(C-Tick), UL(CUL), VCCI |
| Garantie | Warranty | 36months |
| Zubehör | Keyboard Interface | N/A |
| | Mouse Interface | N/A |
| | Power Cord | 1 |
| | AC Adaptor | 1 |
| | Warranty Card | N/A |
| | Quick Guide | 3 |
| | User Manual | N/A |
| | VESA Mount kit | N/A |
| | Keyboard | N/A |
| | Mouse | N/A |
| | Power Switch | N/A |
| Barcode Info | EAN | 4711377424707 |
| Model | Part No | 9S6-B21011-018 |
| | MKT Name | PRO DP10 A14MG |
| | MKT Spec | PRO DP10 A14MG-018AT |
| | Color | ID1/HDMI+LAN Black-Black-Black |
| | SKU Number | 00B21011-018 |
| | Model | B210 |
| | Entity MKT Name | PRO DP10 A14MG-018AT |
| Security | TPM module | dTPM |
| | Chassis Lock | Kensington Lock |
| | Chassis Intrusion | Support |

"2026-05-23 Changes to the product specifications and errors excepted. The product presentation may differ from the product. Microsoft, Windows, the Windows logo, and DirectX are trademarks or registered trademarks of Microsoft Corporation in the United States and / or other countries. Intel, the Intel logo, Intel Inside, the Intel Inside logo, Intel Core and Core Inside are trademarks of Intel Corporation in the US and other countries. Other trademarks and trade names refer to the respective owners or their products."