



Link+ Pro Rauchmelder

XS0B-MR

Technische Spezifikationen

Product Name	Smoke Alarm	Power Supply	3 V CR123A lithium battery × 1 (replaceable)
Battery Life	5 years	Maximum Service Life	10 years
Operating Temperature	40–100°F (4.4–37.8°C)	Operating Relative Humidity	≤ 85% RH (non-condensing)
Alarm Noise Level	≥ 85 dB at 10 ft (3 m) @ 3.2 ± 0.3 kHz pulsing alarm	Silence Duration	≤ 9 minutes
Maximum Number of Interconnected Units	24 wireless units (only compatible with X-Sense Link™ Pro and Link™ wireless alarms)	Transmission Range	Over 1,640 ft (500 m) in open air