

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2023/1669

1. **Samsung**

2. **SM-X135F**

3. **General product parameters:**

Parameter		Value
4. Device type		Tablet
5. Operating system		Android
6. Energy efficiency class		D
7. Battery user-replaceable		No
8. Battery endurance per cycle (ENDdevice [h])		93
9. Battery endurance in cycles – default settings [cycles]		1200
10. Rated battery capacity (Crated [mAh])		4980
11. Shipped with protective cover		No
12. Repeated free fall reliability test – falls without defect [n]		104
13. Repeated free fall reliability test – falls without defect, tested in fully extended state [n]		n.a.
14. Repeated free fall reliability class		C
15. Ingress protection rating		IP52
16. Specified immersion depth in water, in case of IPx8 [m]		n.a.
17. Screen scratch resistance on Mohs hardness scale		5
18. Charger	Required output power [W]	10
	Receptacle type (at device end)	USB_C

Repairability information:

19. Minimum guaranteed availability of operating system security updates, corrective updates and functionality updates(a)(b)(years)	5
20. Repairability Class (based on the index below)	C
21. Repairability Index	2.72
21a. Disassembly Depth (SDD) score	2.55
21b. Fasteners (type) score (SF)	2.80
21c. Tools (type) score (ST)	3.10
21d. Spare Part score (SSP)	2.00
21e. Software Updates (duration) score (SSU)	1.00
21f. Repair Information score (SRI)	5.00
22. Weblink to information on spare parts availability for professional repairers and end users	https://www.samsung.com/uk/support/self-repair-and-spares-parts/
23. Weblink to repair instructions for end-users	https://www.samsung.com/
24. Weblink to indicative pre-tax prices	https://www.samsung.com/uk/support/self-repair-and-spares-parts/

Additional information

25. Minimum duration of the guarantee offered by the supplier [months]	24
Supplier's address	Samsung, PO Box 12987 Blackrock, Co. Dublin, Ireland

No.	BG	ES	CS	DA	DE	ET	EL	FR
1.	Търговска марка	Marca comercial	Ochranná známka	Handelsbetegnelse	Handelsmarke	Kaubamärk	Εμπορικό σήμα	Marque de fabrique
2.	Идентификатор на модела	Identificador del modelo	Identifikační značka modelu	Modellens identifikationskode	Modellkennung	Mudelitühis	Αναγνωριστικό του μοντέλου	Référence du modèle
3.	Основни параметри на продукта:	Parámetros generales del producto:	Obecné parametry výrobku:	Generelle produktparametre:	Allgemeine Produktparameter:	Toote üldnäitajad:	Γενικές παράμετροι του προϊόντος:	Paramètres généraux du produit:
4.	Тип на устройството	Tipo de dispositivo	Typ zařízení	Type enhed	Gerätetyp	Seadme liik	Τύπος συσκευής	Type d'appareil
5.	Операциона система	Sistema operativo	Operační systém	Operativsystem	Betriebssystem	Operatsioonisüsteem	Λειτουργικό σύστημα	Système d'exploitation
6.	Клас на енергийна ефективност	Clase de eficiencia energética	Třída energetické účinnosti	Energieeffektivitetsklasse	Energieeffizienzklasse	Energiaühutuse klass	Τάξη ενεργειακής απόδοσης	Classe d'efficacité énergétique
7.	Батерията може да се сменя от потребителя	Batería sustituable por el usuario	Baterie podporující výměnu uživatelem	Batteri kan udskiftes af brugeren	Vom Nutzer auswechselbare Batterie	Aku on kasutaja poolt asendatav	Μπαταρία που μπορεί να αντικατασταθεί από τον χρήστη	Batterie remplaçable par l'utilisateur
8.	Издръжливост на батерията за един цикъл (ENDdevice [h])	Autonomía de la batería por ciclo (ENDdevice [h])	Výdrž baterie na jeden cyklus (ENDdevice [h])	Batteriholdbarhed pr. cyklus (ENDdevice [h])	Batterielaufzeit pro Zyklus (ENDdevice [h])	Aku vastupidavus tsükli kohta (ENDdevice [h])	Αντοχή μπαταρίας ανά κύκλο (ENDdevice [h])	Endurance de la batterie par cycle (ENDdevice [h])
9.	Издръжливост на батерията в цикли — настройки по подразбиране [цикли]	Autonomía de la batería en ciclos — configuración por defecto [ciclos]	Výdrž baterie v cyklech — výchozí nastavení [cykly]	Batteriholdbarhed i cyklusser — standardindstillinger [cyklusser]	Batterielaufzeit in Zyklen — Standardeinstellungen [Zyklen]	Aku vastupidavus tsükliite arvuna — vaikeseaded [tsükliid]	Αντοχή μπαταρίας σε κύκλους — προεπιλεγμένες ρυθμίσεις [κύκλοι]	Endurance de la batterie en cycles — réglages par défaut [cycles]
10.	Обявен капацитет на батерията (Crated [mAh])	Capacidad asignada de la batería (Crated [mAh])	Zaručená kapacita baterie (Czaručená [mAh])	Nominel batterikapacitet (Crated [mAh])	Nennkapazität der Batterie (Crated [mAh])	Aku nimimahutavus (Crated [mAh])	Ονομαστική χωρητικότητα μπαταρίας (Crated [mAh])	Capacité nominale de la batterie (Crated [mAh])
11.	Доставя се със защитен калъф	Suministrado con funda protectora	Dodáváno s ochranným krytem	Afsendt med beskyttelsescover	Versand mit Schutzabdeckung	Tarnitakse koos kaitsekattega	Αποστέλλεται με προστατευτικό κάλυμμα	Livré avec étui de protection
12.	Изпитване за надеждност при многократно свободно падане — падане без повреждане [n]	Ensayo de fiabilidad en caída libre repetida-caídas sin deterioro [n]	Zkouška spolehlivosti po opakovaném volném pádu – pády bez závady [n]	Prøvning af holdbarhed ved gentagne fald — fald uden defekter [n]	Prüfung der Zuverlässigkeit nach wiederholtem freien Fall — Stürze ohne Defekt [n]	Korduvale mahakukkumisele (vabalangemine) vastupidavuse katse – defekte mittetekitav kukkumiste arv [n]	Δοκιμή αξιοπιστίας κατόπιν επαναληπμένης ελεύθερης πτώσης — πτώση χωρίς εμφάνιση ελαττώματος [n]	Essai de fiabilité en ce qui concerne la résistance aux chutes libres répétées – chutes sans défaillance [n]
13.	Изпитване за надеждност при многократно свободно падане — падане без повреждане, изпитано в напълно разгънато състояние [n]	Ensayo de fiabilidad en caída libre repetida – caídas sin deterioro, ensayo realizado en estado totalmente extendido [n]	Zkouška spolehlivosti po opakovaném volném pádu – pády bez závady, zkoušeno v plně rozloženém stavu [n]	Prøvning af holdbarhed ved gentagne fald — fald uden defekter prøvet i fuldt udfoldet tilstand				

No.	GA	HR	IT	LV	LT	HU	MT	NL
1.	Trádmharc	Zaštitni znak	Marchio	Preču zīme	Prekės ženklas	Védjegy	Trademark	Handelsmerk
2.	Aitheantóir múnla	Identifikációs oznaka modela	Identificativo del modello	Modeļa identifikators	Modelio žymuo	Modellazonosító	Identifikatur tal-mudell	Typeaanduiding
3.	Paraiméadair ghinearálta an tairge:	Opći parametri proizvoda:	Parametri generali del prodotto:	Vispārējie ražojuma parametri:	Bendrieji gaminio parametrai:	Általános termékparaméterek:	Parametri generali tal-prodott:	Algemene productparameters:
4.	Cineál an ghairis	Vrsta uređaja	Tipo di dispositivo	Ierīces veids	Prietaiso tipas	Eszköztípus	Tip ta' apparat	Soort apparaat
5.	Córas oibriúcháin	Operativni sustav	Sistema operativo	Operētājsistēma	Operacinė sistema	Operációs rendszer	Sistema operatorja	Besturingssysteem
6.	Aicme éifeachtúlachta fuinninnh	Razred energetske učinkovitosti	Classe di efficienza energetica	Energoefektivitātes klase	Energijos vartojimo efektyvumo klasė	Energiahatékonysági osztály	Klassi tal-effiċjenza enerġetika	Energie-efficiëntieklasse
7.	Ceallra in-athsholáithraithe d'úsáideoir	Bateriju može zamijeniti korisnik	Batteria sostituibile da parte dell'utente	Lietotājam nomaināma baterija	Baterija gali pakeisti naudotojas	Az akkumulátor a felhasználó által cserélhető	Batterija tista' tinbidel mill-utent	Batterij vervangbaar door de gebruiker
8.	Buaneasmhacht ceallraí in aghaidh an tithrialla (ENDgaires [hl])	Izdržljivost baterije po ciklusu (ENDdevice [hl])	Durata della batteria per ciclo (ENDdevice [hl])	Baterijas izturība vienā ciklā (ENDdevice [hl])	Baterijos patvarumas per ciklą (ENDdevice [hl])	Az akkumulátor ciklusonkénti tartóssága (ENDdevice [hl])	Durabbiltà tal-batterija għal kull ciklu (ENDapparāt [hl])	Batterijduur per cyclus (ENDdevice [hl])
9.	Buaneasmhacht ceallraí i dithrialla — réamshocrúithe [timthrialta]	Izdržljivost baterije u ciklusu — zadane postavke [ciklusi]	Durata della batteria in cicli — impostazioni predefinite [cicli]	Baterijas cikliskā izturība — noklusējuma iestatījumi [ciklos]	Baterijos patvarumas ciklais — numatytosios nuostatos [ciklais]	Az akkumulátor ciklusos tartóssága — alapértelmezett beállítások [ciklusok]	Durabbiltà tal-batterija f'cikli — konfigurazzjonijiet prestabbilti [cikli]	Batterij in cycli — standaardinstellingen [cycli]
10.	Toillleadh ceallraí (C ráitaithe [mAh])	Nazivni kapacitet baterije (Crated [mAh])	Capacità nominale della batteria (Crated [mAh])	Baterijas nominālā kapacitāte (Crated [mAh])	Vardinės baterijos galia (Crated [mAh])	Az akkumulátor névleges kapacitása (Crated [mAh])	Kapaċitá nominali tal-batterija (Cnom [mAh])	Nominaal batterijvermogen (Crated [mAh])
11.	Seolta le cumhdach cosanta	Isporučeno sa zaštitnom oblogom	Commercializzato con custodia protettiva	Piegādāts ar aizsargapvalku	Vežama su apsaugine dangą	Védőburkolattal szállítva	Fornut b'għatu protettiv	Verzonden met beschermende afdekking
12.	Tástáil iontaofachta saorthime arís agus arís eile — titimí gan fabht, [n]	Ispitivanje pouzdanosti nakon ponovljenog slobodnog pada — broj padova bez kvara [n]	Prova di affidabilità in caso di caduta libera ripetuta — cadute senza riportare difetti [n]	Vairākkārtējas kritienizturības tests — kritienu skaits, pēc kuriem nav radies defekts [				

No.	PL		PT		RO		SK		SL		FI		SV	
1.	Znak towarowy		Marca comercial		Marca comercială		Ochranná známka		Blagovna znamka		Tavaramerkki		Varumärke	
2.	Identyfikator modelu		Identificador de modelo		Identificatorul modelului		Identifikačný kód modelu		Identifikacijska oznaka modela		Mallitunniste		Modellbeteckning	
3.	Ogólne parametry produktu:		Parâmetros gerais do produto:		Parametrii generali ai produsului:		Všeobecné parametre výrobku:		Splošni parametri izdelka:		Yleiset tuoteparametrit:		Allmänna produktparametrar:	
4.	Typ urządzenia		Tipo de dispositivo		Tipul de dispozitiv		Druh zariadenia		Tip naprave:		Laiteen tyyppi		Produkttyp	
5.	System operacyjny		Sistema operativo		Sistemul de operare		Operačný systém		Operacijski sistem		Käyttöjärjestelmä		Operativsystem	
6.	Klasa efektywności energetycznej		Clase de eficiencia energética		Clasa de eficiență energetică		Trieda energetickej účinnosti		Razred energijske učinkovitosti		Energiatohokkuusluokka		Energieffektivitetsklass	
7.	Bateria, którą może wymienić użytkownik		Bateria substituível pelo utilizador		Baterie cu posibilitate de înlocuire de către utilizator		Batería vymeniteľná používateľom		Baterijo lahko zamenja uporabnik		Akku käyttäjän itse vaihdettavissa		Batteri som kan bytas ut av användaren	
8.	Trwałość baterii na cykl (ENDdevice [h])		Durabilidade da bateria por ciclo (ENDdevice [h])		Duranța bateriei pentru fiecare ciclu (ENDdevice [h])		Výdrž batérie v rámci jedného cyklu (ENDdevice [h])		Vzdržljivost baterije na cikel (ENDnaprave [h])		Akun kesto lataussykliä kohti (ENDdevice [h])		Batteriets uthållighet per cykel (ENDdevice [h])	
9.	Trwałość baterii w cyklach – ustawienia domyślne [liczba cykli]		Durabilidade da bateria em número de ciclos – definições predefinidas [ciclos]		Duranța bateriei în cicluri – setări implicite [cicluri]		Výdrž batérie z hľadiska počtu cyklov – predvolené nastavenia [cykli]		Vzdržljivost baterije v cikliih – privzete nastavitve [cikli]		Akun kesto käyttösykleinä – oletusasetuksilla [sykleinä]		Batteriets uthållighet i cykler – standardinställningar [cykler]	
10.	Poj													