


		Material Material	Dimensions Abmessungen [mm]
A	Inner conductor Innenleiter	Steel, copper-plated, silver-plated Stahl, verkupfert + versilbert	Ø 0,51 (7x Ø 0,17)
B	Dielectric Isolierung	PTFE, solid PTFE	Ø 1,52
C	Outer conductor, Braid Außenleiter, Geflecht	Copper, silver-plated Kupfer, versilbert	Ø 1,92
D	Jacket Außenmantel	FEP, brown transparent FEP, bräunlich transparent	Ø 2,5

Änd./ rev. index	Änderungs-Nr. / revision code	Datum/ date	Name/ name	Datum/ date	Name/ name	Gewicht/ weight [g]		
			gez./ drawn	04.03.2009	GB			
			gepr./ appr.	10.03.2009	BJ	ca./approx.		
			Maßstab/ scale	Benennung/ title				 Telegärtner
			2:1	RG-316/U				
			untl. Maße/ dim. without tolerances according to	Untert./doc. type	Zeichnungsnr./ drawing no.		 Maße/ dimensions: mm	
				K	L01000A0002			
				Ersatz für/ replaces				Original : DIN A4
								Blatt/ sheet 1 von/ of 1