

Portable Compressor Cooler 40L

- Strong compressor technology
- Durable design and quiet operation (less than 45dB)
- Adjustable cooling mode:
Fast cooling / Energy saving
- Built-In car battery protection
- Control by ProUser Power App



CoolZ 40

Name		Pro-User CoolZ 40
Art.no.		20411
EAN		8717809204110
Net. capacity		40 liters

Electrical	
Input voltage	220V - 240V
Input DC voltage	12V / 24V
Power consumption	60W
Input AC current	0.26A
Input DC current	5 / 2.5A

Performance	
Classification climate	T / ST / N
Refrigerant	R600a
Cooling system	Compressor
Temperature range	-20°C - +20°C
Noise level	< 45dB

Measurements	
Dimensions	L669 x W374 x D463 mm
Weight	13.8 kg
Package dimensions	L698 x W440 x H517 mm
Package weight	16.1 kg

Included	
• 230V and 12V adapter	• Built-in LED light inside
• Removable wire rack	• Cutting board
• Bottle opener	• Fitting cooling bag

Available accessories	
Stand	20439
Powerbank	20414



Portable Compressor Cooler
CoolZ 40

PRO ELECTRONICS®
USER