

KRUPS

## Krups Virtuoso XP441810 Kaffeemaschine Manuell Espressomaschine 1,1 l

Marke : Krups

Produktfamilie: Virtuoso

Artikel-Code: XP441810

Produktname : XP441810

Krups Virtuoso XP441810. Produkttyp: Espressomaschine, Kaffeezubereitungstyp: Manuell, Fassungsvermögen Wassertank: 1,1 l, Kaffee-Einfüllart: Gemahlener Kaffee, Behälter für gebrühten Kaffee: Tasse, Kapazität (in Tassen): 2 Tassen. Leistung: 1350 W. Produktfarbe: Schwarz, Edelstahl



| Leistungen                           |                   | Kochfunktionen und -programme        |                    |
|--------------------------------------|-------------------|--------------------------------------|--------------------|
| Kaffeezubereitungstyp *              | Manuell           | Zubereitung von Café Ristretto       | ✓                  |
| Behälter für gebrühten Kaffee *      | Tasse             | Zubereitung von Caffè Latte          | ✓                  |
| Kapazität (in Tassen) *              | 2 Tassen          | <b>Ergonomie</b>                     |                    |
| Maximaler Betriebsdruck              | 15 bar            | Steuerung *                          | Tasten             |
| Eingebautes Mahlwerk *               | ✗                 | Eingebautes Display *                | ✗                  |
| Integrierter Milchaufschäumer        | ✓                 | Abnehmbarer Wasserbehälter           | ✓                  |
| Heißwassersystem *                   | ✓                 | Produktfarbe *                       | Schwarz, Edelstahl |
| Heizsystem                           | Thermoblock       | Abnehmbarer Tropfschale              | ✓                  |
| Temperaturregelungstyp               | Elektronisch      | Einfach zu säubern                   | ✓                  |
| Geräteplatzierung *                  | Arbeitsplatte     | <b>Energie</b>                       |                    |
| Produkttyp *                         | Espressomaschine  | Leistung *                           | 1350 W             |
| Automatischer Wasserstopp            | ✓                 | AC Eingangsspannung                  | 220 - 240 V        |
| Fassungsvermögen Wassertank *        | 1,1 l             | Automatische Abschaltung nach (max.) | 28 min             |
| Kaffee-Einfüllart *                  | Gemahlener Kaffee | <b>Gewicht und Abmessungen</b>       |                    |
| <b>Kochfunktionen und -programme</b> |                   | Breite                               | 143 mm             |
| Multi-Getränke *                     | ✓                 | Tiefe                                | 285 mm             |
| Kaffeezubereitung                    | ✓                 | Höhe                                 | 285 mm             |
| Espressozubereitung *                | ✓                 | <b>Verpackungsdaten</b>              |                    |
| Zubereitung von Cappuccino *         | ✓                 | Menge pro Packung                    | 1 Stück(e)         |
| Zubereitung von Caffè Americano      | ✓                 | <b>Lieferumfang</b>                  |                    |
|                                      |                   | Löffel enthalten                     | ✓                  |
|                                      |                   | Milchaufschäumer enthalten           | ✓                  |
|                                      |                   | Stampfer                             | ✓                  |



3016661176449

### Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.