POWER-SUPPLY

MAG A750BN PCIE5

YOUR POWER, RIGHT AWAY



MAG A750BN PCIE5

- PCIe 5.0 Unterstützung (300W)
- 120mm Lüfter
- DC / DC Leistungsdesign
- Aktives PFC Design
- Industrie Schutzfunktionen OVP, OCP, SCP, OPP, OTP

SPECIFICATIONS

Efficiency Rating	80 PLUS Bronze (up to 85%)
Modular	No
Fan Bearing	Sleeve Bearing
Power Watt	750W
Input Voltage	100-240~
Input Frequency	50~60Hz
ATX (24 pin)	1
EPS (4+4 PIN)	2
Fan Size	120 mm
PCI-E 5.0 (16 pin)	1(300W)
Dimension	140mm x 150mm x 86mm / 5.51 x 5.9 x 3.38 inches
PCI-E (6+2 pin)	2
PFC Type	Active PFC
SATA (15 pin)	5
Protection	OCP, OVP, OPP, OTP, SCP
MOLEX (4 pin)	2
FDD (4 pin)	1

MAG A750BN PCIE5					
AC INPUT	100-240V~, 10-5A, 50~60Hz				
DC OUTPUT	+5V	+3.3V	+12V	-12V	+5Vsb
	20A	20A	62.5A	0.3A	2.5A
TOTAL POWER	120W		750W	3.6W	12.5W
			750W		

CONNECTOR

© 2024 Micro-Star Int'l Co.Ltd. MSI is a registered trademark of Micro-Star Int'l Co.Ltd. All rights reserved.

POWER-SUPPLY

MAG A750BN PCIE5

YOUR POWER, RIGHT AWAY

CONNECTOR						
ATX	EPS	PCI-E 5.0	PCI-E	SATA	Molex	FDD
1	2	1	2	5	2	1

Generated 2024-02-20, check for the latest version www.msi.com/datasheet. The information provided in this document is intended for informational purposes only and is subject to change without notice.

© 2024 Micro-Star Int'l Co.Ltd. MSI is a registered trademark of Micro-Star Int'l Co.Ltd. All rights reserved.