



germanengineering

BG 21 Glas-Diagnosewaage

Grafisches Druckmotiv mit "Durchblick"
Großes LCD-Display mit Multi-Anzeige
Ziffernhöhe (Gewichtsanzeige): 25 mm
Körpergewicht, -fett, -wasser, Muskelanteil,
Knochenmasse, Kalorienbedarf (BMR/AMR)
Mit BMI-Berechnung
Interpretation des Körperfetts
Elektroden aus gebürstetem Edelstahl
5 Aktivitätsgrade
10 Speicherplätze
Überlastungsanzeige
180 kg Tragkraft
Einteilung:
• 0,1% für Körperfett, -wasser, Muskelanteil
• 100 g für Gewicht, Knochenmasse
Tap-On-Technik
Abschaltautomatik
Inkl. 2 x 3 V Batterie CR2032
Produktabmessungen: 30 x 31,5 x 2,5 cm

5 Jahre Garantie

Versandereinheit: 4 Transportkarton: -
EAN-Nr.: 42 11125 76430 2
Art.-Nr.: 764.30

BG 21 Glass diagnostic scale

Printing with "see-through"-effect
Large LCD-display with multi display
Digit size (weight display): 25 mm
Body weight, body fat, body water, muscle ratio,
bone mass, calory consumption (BMR/AMR)
With BMI calculation
Interpretation of body fat
Electrodes of brushed stainless steel
5 activity levels
10 memories
Overload indication
180 kg capacity
Division:
• 0,1% body fat, body water, muscle ratio
• 100 g for body weight, bone mass
Tap-on-technology
Automatic switch off
2 x 3 V batteries CR2032 included
Product measurements: 30 x 31.5 x 2.5 cm

5 year guarantee

Sales unit: 4 Shipping carton: -
EAN no.: 42 11125 76430 2
Item number: 764.30