

Datenblatt Art. 918.020

Data sheet | Fiche technique | Scheda tecnica | Fișa tehnică

HDMI Verbindungskabel

Produkteigenschaften		Product attributes	
Länge (L)	5,0m	Length (L)	5,0m
Kabelquerschnitt	28 AWG	Cable diameter (per wire)	28 AWG
Kabeldurchmesser	7,3mm	Cable diameter	7,3mm
Mantelisololation	PVC	Sheath insulation	PVC
Aderisolation	PVC	Wire insulation	PVC
Farbe Mantelisololation	schwarz	Colour Sheath insulation	black
Seite 1 Stecker	HDMI 19-polig	Side 1 Plug	HDMI 19-poles
Seite 2 Stecker	HDMI 19-polig	Side 2 Plug	HDMI 19-poles
Lieferumfang 1x HDMI Verbindungskabel		Scope of delivery 1x HDMI connection cable	
Im Polybeutel		Packed in polybag	
Konformität / Approbation		Conformity / Approval	
Bauart geprüft	RoHS	Type approved	RoHS
Sonstiges		Other	
HDMI 1.3 Standard: 1920x1080 Pixel Max. Auflösung: 4K/60Hz Full HD		HDMI 1.3 standard: 1920x1080 pixel Max. resolution: 4K/60Hz Full HD	

