

KRUPS

Krups EA5008 Vollautomatisch Espressomaschine 2 l

Marke : Krups

Artikel-Code: EA5008E0

Produktname : EA5008

Krups EA5008. Produkttyp: Espressomaschine, Kaffeezubereitungstyp: Vollautomatisch, Fassungsvermögen Wassertank: 2 l, Kaffee-Einfüllart: Kaffeebohnen, Behälter für gebrühten Kaffee: Tasse, Kapazität (in Tassen): 2 Tassen, Eingebautes Mahlwerk. Leistung: 1450 W. Produktfarbe: Schwarz



Leistungen		Leistungen	
Kaffeezubereitungstyp *	Vollautomatisch	Entkalkungsfunktion	✓
Behälter für gebrühten Kaffee *	Tasse	Ursprungsland	China
Kapazität (in Tassen) *	2 Tassen	Kochfunktionen und -programme	
Maximaler Betriebsdruck	15 bar	Multi-Getränke *	✓
Eingebautes Mahlwerk *	✓	Anzahl der Programme	4
Art des Mahlwerks	Metall-Mahlwerk	Espressozubereitung *	✓
Anpassbare Mahloptionen	✓	Zubereitung von Café Ristretto	✓
Anzahl der Mahloptionen	5	Zubereitung von Caffè Lungo	✓
Fassungsvermögen Kaffeebohnen	260 g	Ergonomie	
Kapazität des Behälters für gemahlene Kaffeebohnen	9 Tassen	Steuerung *	Tasten, Drehregler
Einstellbare Stärke des Kaffees *	✓	Eingebautes Display *	✗
Anzahl der Kaffeestärkeneinstellungen	2	Abnehmbarer Wasserbehälter	✓
Milchtank	✓	Produktfarbe *	Schwarz
Milchtank-Kapazität	0,3 l	Abnehmbarer Tropfschale	✓
Höhenverstellbarer Kaffeeausguss	✓	Tassenhalter	✓
Heißwassersystem *	✗	Energie	
Anzahl der Temperatureinstellungen	1	Leistung *	1450 W
Dampfleitung	✓	AC Eingangsspannung	220 - 240 V
Spülfunktion	✓	AC Eingangsfrequenz	50 Hz
Geräteplatzierung *	Arbeitsplatte	Gewicht und Abmessungen	
Produkttyp *	Espressomaschine	Breite	240 mm
Fassungsvermögen Wassertank *	2 l	Tiefe	346 mm
Kaffee-Einfüllart *	Kaffeebohnen	Höhe	364 mm
Alarmleuchte Entkalkung	✓	Gewicht	7,06 kg

Verpackungsdaten

Menge pro Packung	1 Stück(e)
Verpackungsbreite	287 mm
Verpackungstiefe	381 mm
Verpackungshöhe	461 mm
Paketgewicht	9,08 kg



3016667299890

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity. Automated scraping, data mining, or harvesting for the purpose of training machine learning models, neural networks, or artificial intelligence systems is strictly prohibited without a commercial license.