BJZ

Shielding Tape Datenblatt



Shielding-Tape, leitfähig

Material:	Ethylen-Propylen-Gummi	
Dicke:	ca. 0,762 mm	
Farbe:	schwarz	
Reißkraft:	ca. 225 lbs/zoll	
Zugdehnung:	ca. 500 %	
Temperaturbereich:	90°C konstant, 130°C kurzzeitig	
Widerstand:	ca. 10^4 Ohm (bei ca. 50 % relativer Luftfeuchte)	
Eigenschaften:	UV-beständig	
Breite:	19 mm	38 mm
Länge pro Rolle:	4,6 m	9,1 m
Bestell-Nr.:	**Z-208-8212**	**Z-195-3846**

BJZ GmbH & Co. KG
Berwanger Str. 29 • D-75031 Eppingen/Richen
Telefon: +49 -7262-1064-0
Fax: +49 -7262-1063
E-Mail: info@bjz.de
Web: www.bjz.de

BJZ

Shielding Tape datasheet



Shielding-Tape, conductive

material:	Ethylen-Propylen-Rubber (EPR)
thickness:	approx. 0,762 mm
color:	black
tensile strength:	ca. 225 lbs/inch
elongation:	ca. 500 %
temperature range:	90°C constantly, 130°C emergency overload
resistance:	ca. 10^4 Ohm (on ca. 50 % relative humidity)
features:	UV-resistant

width:	19 mm	38 mm
length per roll:	4,6 m	9,1 m
Order-no.:	**Z-208-8212**	**Z-195-3846**

BJZ GmbH & Co. KG
Berwanger Str. 29 • D-75031 Eppingen/Richen
Telefon: +49 -7262-1064-0
Fax: +49 -7262-1063
E-Mail: info@bjz.de
Web: www.bjz.de