



Fan Module for LogiLink and Canovate Wall Mounted Cabinets

Technical Features

Material: 0.8 mm steel Air Flow: 95–115 CFM

Operating Voltage: AC 220–240 V, 50/60 Hz

Fan Speed: 2700–3100 rpm **Noise**: 44–49 dB (A)

These fan units are required for the ventilation of wall-mounted cabinets. They are installed under the top

cover of the wall-mounted cabinet.

It is equipped with a thermostat, fuse and power cable.

Fan Module - RAL 9005 Black

H (mm)	D (mm)	W (mm)	Number of Fans	Weight (kg)	Part No.	EAN Code
39	135	326	1	1.27	FAW101B	8698800001409
39	135	326	2	1.80	FAW102B	8698800001423

Fan Module - RAL 7035 Light Grey

H (mm)	D (mm)	W (mm)	Number of Fans	Weight (kg)	Part No.	EAN Code
39	135	326	1	1.27	FAW101G	8698800001393
39	135	326	2	1.80	FAW102G	8698800001416





