

HG 20-600 (602066500) Hot Air Gun
metaBOX 145

Order no. 602066500
EAN 4061792186057



Product may differ from Image

- Versatile hot air gun with adjusting wheel for easy, variably adjustment of the temperature
- High-quality ceramic heating, powerful motor and optimum device cooling for long service life
- Wide range of uses: removal of varnish, shaping, crimping, welding and much more
- Ergonomic design and handle with non-slip soft-grip surface provides convenient handling
- Safe stationary application due to large non-slip floor space

Technical data**Characteristics**

Air volume	150 / 300 / 500 l/min // 5 / 11 / 18 cfm
Number of air volume levels	3
Air temperature	80 - 600 °C // 176 - 1112 °F
Number of air temperature levels	infinitely variable
Input power max.	2000 W
Weight (without power cable)	0.62 kg / 22 oz
Cable length	2.2 m / 7 ft

Scope of delivery

Wide jet nozzle (50 mm)
metaBOX 145
Wrap around nozzle
Reducing nozzle (9 mm)