

Manhattan DisplayPort 1.4 Cable, 8K@60hz, 2m, PVC Cable, Male to Male, With Latches, Fully Shielded, Black, Lifetime Warranty, Polybag - DisplayPort-Kabel - DisplayPort (M)

zu DisplayPort (M) - DisplayPort 1.4 - 300 V - 2 m - Support von 4K 120 Hz - Support von 8K 60 Hz - Schwarz



Gruppe	Kabel / Adapter
Hersteller	Manhattan
Hersteller Art. Nr.	355575
EAN/UPC	0766623355575

Beschreibung

Manhattan DisplayPort 1.4 Cable, 8K@60hz, 2m, PVC Cable, Male to Male, With Latches, Fully Shielded, Black, Lifetime Warranty, Polybag - DisplayPort-Kabel - DisplayPort (M) zu DisplayPort (M) - DisplayPort 1.4 - 300 V - 2 m - Support von 4K 120 Hz, Support von 8K 60 Hz - Schwarz

Hauptmerkmale

Produktbeschreibung	Manhattan DisplayPort 1.4 Cable, 8K@60hz, 2m, PVC Cable, Male to Male, With Latches, Fully Shielded, Black, Lifetime Warranty, Polybag - DisplayPort-Kabel - DisplayPort zu DisplayPort - 2 m
Typ	DisplayPort-Kabel
Technologie	Dreifachisolierung
Besonderheiten	Support von 4K 120 Hz, Support von 8K 60 Hz, Display Stream Compression 1.2 (DSC), HDR-Support, 32 unkomprimierte digitale Audiokanäle, DisplayPort Multi-Stream Transport (MST), High Bit Rate 3 (HBR3), 32,4 Gb/s gesamte Bandbreite, Dolby Atmos
Länge	2 m
Anschluss	20-poliger DisplayPort - männlich
Stecker (zweites Ende)	20-poliger DisplayPort - männlich
Bewertete Spannung	300 V
Produktzertifizierungen	DisplayPort 1.4
Farbe	Schwarz
Verpackung	Polybeutel

Technische Daten © 1WorldSync. Technische Änderungen und Irrtümer vorbehalten.