

Manhattan VGA Monitor Cable (with Ferrite Cores), 3m, Black, Male to Male, HD15, Cable of higher SVGA Specification (fully compatible)

Shielding with Ferrite Cores helps minimise EMI interference for improved video transmission - Lifetime Warranty - Polybag - VGA-Kabel - HD-15 (VGA) (M) zu HD-15 (VGA) (M) - DC 300 V - 3 m - geformt - Daumenschrauben - Schwarz



Gruppe	Kabel / Adapter
Hersteller	Manhattan
Hersteller Art. Nr.	317733
EAN/UPC	0766623317733

Beschreibung

Manhattan VGA Monitor Cable (with Ferrite Cores), 3m, Black, Male to Male, HD15, Cable of higher SVGA Specification (fully compatible), Shielding with Ferrite Cores helps minimise EMI interference for improved video transmission, Lifetime Warranty, Polybag - VGA-Kabel - HD-15 (VGA) (M) zu HD-15 (VGA) (M) - DC 300 V - 3 m - geformt, Daumenschrauben - Schwarz

Hauptmerkmale

Produktbeschreibung	Manhattan VGA Monitor Cable (with Ferrite Cores), 3m, Black, Male to Male, HD15, Cable of higher SVGA Specification (fully compatible), Shielding with Ferrite Cores helps minimise EMI interference for improved video transmission, Lifetime Warranty, Polybag - VGA-Kabel - HD-15 (VGA) zu HD-15 (VGA) - 3 m
Typ	VGA-Kabel
Technologie	Abgeschirmt
Besonderheiten	Geformt, Daumenschrauben, Zugentlastung, EMI-Schutz, 2 Ferritkerne
Länge	3 m
Anschluss	15-polige HD D-Sub (HD-15) - männlich
Stecker (zweites Ende)	15-polige HD D-Sub (HD-15) - männlich
Bewertete Spannung	DC 300 V
Farbe	Schwarz

Technische Daten © 1WorldSync. Technische Änderungen und Irrtümer vorbehalten.