

Kioxia PM5-V Series KPM51VUG6T40 - SSD - 6400 GB - intern - 2.5" (6.4 cm)

SAS 12Gb/s

Gruppe	Festplatten
Hersteller	Kioxia
Hersteller Art. Nr.	KPM51VUG6T40
EAN/UPC	4047999611059



Beschreibung

KIOXIA PM5-V Series KPM51VUG6T40 - SSD - 6400 GB - intern - 2.5" (6.4 cm) - SAS 12Gb/s

Hauptmerkmale

Produktbeschreibung	KIOXIA PM5-V Series KPM51VUG6T40 - SSD - 6400 GB - SAS 12Gb/s
Typ	Solid State Drive - intern
Kapazität	6400 GB
NAND-Flash-Speichertyp	3D triple-level cell (TLC)
Formfaktor	2.5" (6.4 cm)
Schnittstelle	SAS 12Gb/s
Datenübertragungsrate	1.2 GBps
Merkmale	Dual Port, End-to-End-Datenschutz, T10 Data Integrity Field (DIF), Enterprise, Mixed-Use, Multi-Stream Write, Stromausfallschutz (SAS), Power Disable Pin (Pin3), 64-layer 3D BiCS FLASH, MultiLink SAS-Support
Abmessungen (Breite x Tiefe x Höhe)	69.85 mm x 100.45 mm x 15 mm
Gewicht	130 g

Technische Daten © 1WorldSync. Technische Änderungen und Irrtümer vorbehalten.