

Manhattan TV & Monitor Mount (inc media player storage area), Wall, Tilt, 1 screen, Screen Sizes: 37-65", Black, VESA 200x200 to 600x400mm, Max 35kg, LFD, Lifetime Warranty - Klammer - für LCD TV - Stahl - Bildschirmgröße: 94-177.8 cm (37"-70")



Wandmontage

Gruppe	Zubehör TFT/LCD-TV
Hersteller	Manhattan
Hersteller Art. Nr.	461467
EAN/UPC	0766623461467

Beschreibung

Manhattan TV & Monitor Mount (inc media player storage area), Wall, Tilt, 1 screen, Screen Sizes: 37-65", Black, VESA 200x200 to 600x400mm, Max 35kg, LFD, Lifetime Warranty - Klammer - für LCD TV - Stahl - Bildschirmgröße: 94-177.8 cm (37"-70") - Wandmontage

Hauptmerkmale

Produktbeschreibung	Manhattan TV & Monitor Mount (inc media player storage area), Wall, Tilt, 1 screen, Screen Sizes: 37-65", Black, VESA 200x200 to 600x400mm, Max 35kg, LFD, Lifetime Warranty - Klammer - für LCD TV
Produkttyp	Klammer - Wandmontage
Abmessungen (Breite x Tiefe x Höhe)	64.4 cm x 8.9 cm x 42.5 cm
Neigung	-12 ° bis 12 °
Anpassungen	Neigung
Empfohlene Verwendung	LCD TV
Empfohlene Display-Größe	94-177.8 cm (37"-70")
VESA-Halterung	200 x 200 mm, 400 x 300 mm, 400 x 200 mm, 400 x 400 mm, 600 x 400 mm, 300 x 200 mm, 300 x 300 mm
Max. Ladegewicht	35 kg
Material	Stahl

Technische Daten © 1WorldSync. Technische Änderungen und Irrtümer vorbehalten.