

Intellinet Gigabit RJ45 Copper SFP Optical Transceiver Module, 1000Base-T (RJ-45)

port - 100m - Equivalent to Cisco GLC-T - Three Year Warranty - SFP (Mini-GBIC)-Transceiver-Modul - GigE - 10Base-T - 100Base-TX - 1000Base-T - RJ-45 - bis zu 100 m



Gruppe	Kabel / Adapter
Hersteller	Intellinet
Hersteller Art. Nr.	523882
EAN/UPC	0766623523882

Beschreibung

Intellinet Gigabit RJ45 Copper SFP Optical Transceiver Module, 1000Base-T (RJ-45) port, 100m, Equivalent to Cisco GLC-T, Three Year Warranty - SFP (Mini-GBIC)-Transceiver-Modul - GigE - 10Base-T, 100Base-TX, 1000Base-T - RJ-45 - bis zu 100 m

Hauptmerkmale

Produktbeschreibung	Intellinet Gigabit RJ45 Copper SFP Optical Transceiver Module, 1000Base-T (RJ-45) port, 100m, Equivalent to Cisco GLC-T, Three Year Warranty - SFP (Mini-GBIC)-Transceiver-Modul - GigE
Gerätetyp	SFP (Mini-GBIC)-Transceiver-Modul - RJ-45
Formfaktor	Plug-in-Modul
Verdrahtungstyp	10Base-T, 100Base-TX, 1000Base-T
Datenübertragungsrate	1.25 Gbps
Data Link Protocol	GigE
Maximaler Übertragungsbereich	100 m
Abmessungen (Breite x Tiefe x Höhe)	1.4 cm x 6.7 cm x 1.2 cm
Gewicht	23 g

Technische Daten © 1WorldSync. Technische Änderungen und Irrtümer vorbehalten.