

ThinkVision M14 61DDUAT6EU

Product
ThinkVision M14

Region
EMEA

Color
Black

Panel
In-Plane Switching

Display Size
14"

View Area
309.31x173.99 mm

Resolution
1920x1080

Aspect Ratio
16:9

Pixel Pitch
0.1611x0.1611 mm

Dot / Pixel Per Inch
157 dpi

Brightness
300 nits

Contrast Ratio
700:1

Pixel Response Time
6 ms

Color Gamut
72%

View Angle (H / V)
178 / 178

Stand
Tilt, Height Adjust Stand

Side Bezel Width
5.48 mm

Dimensions with Stand (HxWxD)
209.03x323.37x96.54 mm

Power Consumption (Typical / Maximum)
6W / 7.5W

Power Adapter
External

Weight (Including Stand)
1.26lb / 0.57kg

Warranty
3-year

ENERGY STAR
ENERGY STAR 7.1

TCO
None

EPEAT
Bronze

Presets / User Settings
26 / 20

On Screen Display
OSD, 2 Languages

USB Port
USB 3.1 Type-C x 2

Speaker
None

Camera
None

Multiple Input
USB

Monitor Cable
USB

CPU / Platform
None / None

Display Ram / Storage / Card Slot
None / None / None

Wireless / Ethernet / Bluetooth
None / None / None

Touch Screen / Digitizer Pen / Battery
None / None / None

Operating System
Support Windows 7, Windows 8, Windows 8.1, Windows 10

Ann Date (mm/yy)
06/19



WWW.LENOVO.COM

This publication was developed for products and services offered in the United States and E.M.E.A countries. Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication “as is” without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<http://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2019. All rights reserved.



Lenovo™



PORTABLE USB-C MONITOR CRAFTED FOR IMPROVED PRODUCTIVITY

The ThinkVision M14 is an ultraslim and ultralight mobile monitor. Its 14-inch screen helps you extend your workspace comfortably no matter where work takes you. Compatible with notebooks of any screen size that come with an advanced USB Type-C port*, the ThinkVision M14 can either extend or duplicate your notebook display with one plug. The USB Type-C ports on either side allow both left- and right-handed users to work efficiently, and the ergonomic design enhances user experience. Packed with impressive portability, connectivity, and flexibility features, the ThinkVision M14 is ideal for mobile productivity.



Extreme Portability



Superior Connectivity



Remarkable Flexibility

ACHIEVE TARGETS ON THE GO

The ThinkVision M14 boosts productivity with its thin and light form factor. Weighing 570g, this 4.4mm sleek mobile monitor enables easy portability. The stylish design with a Full HD, IPS display provides vivid lifelike visuals, ensuring you never miss out on any detail. With a brightness of 300 nits, the ThinkVision M14 offers a stunning visual experience while consuming content online.



4.4mm sleek: approximately as thin as two USD \$1 coins



Weight
570g



Screen Size
14 inches




Brightness
300 nits (Typical)



EXPERIENCE ADVANCED CONNECTIVITY

Two innovative USB Type-C ports on either side of the monitor make connectivity effortless. These ports support both power and video delivery simultaneously from a single port. The ThinkVision M14 also offers a 'power pass through' design that powers the mobile monitor by an adapter and charges the notebook at the same time. This feature is suitable for smartphones or notebooks with one USB Type-C port*. The ambidextrous design of this monitor enhances user comfort.



Ambidextrous design: built to enable both left- and right-handed users to work with ease



USB Ports
2 x USB Type-C




Cable
USB Type-C to C

WORK THE WAY YOU LIKE

The ThinkVision M14 with its admirable flexibility is built for varied job roles. With a tilt angle of -5°-90°, you can position your monitor in a way that suits your style. Compare content with ease even as you use laptops of different screen sizes with the ergonomic height adjustable foot. Also, you can wall mount your monitor effortlessly with mounting support for a hands-free viewing experience. The advanced low blue light technology minimizes eye strain, making extended working hours easy.



Height Adjustable Foot
Tilt 0°-90°



Monitor Stand
Tilt -5°-90°



Eye-care Technology
Low blue light



Height Adjustable Foot
Tilt angle: 0°-90°

Monitor Stand
Tilt angle: -5°-90°

Remarkable flexibility: position the monitor in the way that suits your style

*For charging usage, a Lenovo branded 65W adapter (Part No.: SA10E75874) is recommended

TECH SPECS

<p>LCD PANEL</p> <p>Panel Size 14-inch</p> <p>Screen Dimensions (W x H, mm) 309.31 x 173.99 mm</p> <p>Panel Type In-Plane Switching</p> <p>Backlight WLED</p> <p>Aspect Ratio 16:9</p> <p>Resolution 1920 x 1080</p> <p>Pixel Pitch (H x V, mm) 0.1611 x 0.1611 mm</p> <p>Dot/Pixel Per Inch (DPI/PPI) 157</p> <p>Viewing angle (H x V @ CR 10:1) 178° / 178°</p> <p>Response Time (typical) 6ms with OD</p> <p>Refresh Rate 60 Hz</p> <p>Brightness (typical) 300 cd/m²</p> <p>Contrast Ratio (typical) 700:1</p> <p>Dynamic Contrast Ratio (typical) 3M:1</p> <p>Colour Gamut NTSC (CIE 1931) 72%</p> <p>Color Support (typical) 16.7 Million</p> <p>Color Depth 8bit (6bit + FRC)</p> <p>Anti-Glare Yes</p>	<p>Power Consumption Switch-Off Mode < 0.3 W</p> <p>USB Type-C/Power Delivery Up to 65 W</p> <p>Power Supply External (no adapter bundle)</p> <p>Voltage Required DC 5 V to 20 V</p> <p>MECHANICAL</p> <p>Tilt Angle (front/back) -5° / 90°</p> <p>Mounting Support Yes (100 mm)</p> <p>Kensington™ Lock Slot Yes</p> <p>Cable Management Yes</p> <p>Bezel Color Raven Black</p> <p>Bezel Width (Side) 5.48mm</p> <p>Bezel Width (top / bottom) 5.47 mm / 23.87 mm</p> <p>DIMENSIONS</p> <p>Size Packed (D x H x W) (mm / inch) 276 x 61 x 402 mm / 10.87 x 2.40 x 15.83 inches</p> <p>Size Unpacked w/stand (D x H x W) (mm / inch) (Lowest position) 96.54 x 209.03 x 323.37 mm / 3.8 x 8.23 x 12.73 inches</p> <p>Size Unpacked w/stand (D x H x W) (mm / inch) (Highest position) 96.54 x 220.03 x 323.37 mm / 3.8 x 8.66 x 12.73 inches</p> <p>Stand base footprint area (mm²) 260.87 x 69.55 mm / 10.27 x 2.74 inches</p> <p>Weight Packed (kg / lbs.) 1.67 kg / 3.67 lbs.</p> <p>Weight Unpacked (kg / lbs.) 0.57 kg / 1.26 lbs.</p>	<p>ENVIRONMENTAL</p> <p>Temperature - Operating 0° to 40°C</p> <p>Temperature - Non-operating -20° to 60°C</p> <p>Humidity - Operating 30 to 80%</p> <p>Humidity - Non-operating 30 to 90%</p> <p>Altitude - Operating 0 to 5000 m</p> <p>Altitude - Non-operating 0 to 40,000 ft</p> <p>Arsenic-free Glass Yes</p> <p>PVC free Yes</p> <p>Mercury free Yes</p> <p>PCC % of plastic resins 85%</p> <p>WARRANTY</p> <p>Geography Availability WW</p> <p>Warranty 3 Years</p> <p>CERTIFICATIONS</p> <p>ENERGY STAR® Rating 7,1</p> <p>CCC Yes</p> <p>EPEAT Bronze</p> <p>RoHS (EU 2002/95/EC) Yes (Arsenic free / Pb free / Mercury free)</p> <p>Windows Certification Windows 7 / 10</p> <p>Image Quality Capability ISO 9241-307</p> <p>China Energy Efficiency Standard Tier 2</p> <p>Low Blue Light / Eye Comfort Yes (Low BlueLight)</p>
--	--	--

ThinkVision M14

