

Manhattan SVGA Y Cable, HD15, 15cm, Male to Females, Splits an SVGA connection between two monitors, Compatible with VGA, Fully Shielded, Black, Lifetime Warranty, Polybag - VGA-Splitter - HD-15 (VGA)

(M) zu HD-15 (VGA) (W) - DC 300 V - 15 cm - geformt - Daumenschrauben - Schwarz



| | |
|---------------------|-----------------|
| Gruppe | Kabel / Adapter |
| Hersteller | Manhattan |
| Hersteller Art. Nr. | 304559 |
| EAN/UPC | 0766623304559 |

Beschreibung

Manhattan SVGA Y Cable, HD15, 15cm, Male to Females, Splits an SVGA connection between two monitors, Compatible with VGA, Fully Shielded, Black, Lifetime Warranty, Polybag - VGA-Splitter - HD-15 (VGA) (M) zu HD-15 (VGA) (W) - DC 300 V - 15 cm - geformt, Daumenschrauben - Schwarz

Hauptmerkmale

| | |
|------------------------|---|
| Produktbeschreibung | Manhattan SVGA Y Cable, HD15, 15cm, Male to Females, Splits an SVGA connection between two monitors, Compatible with VGA, Fully Shielded, Black, Lifetime Warranty, Polybag - VGA-Splitter - HD-15 (VGA) zu HD-15 (VGA) - 15 cm |
| Typ | VGA-Splitter |
| Technologie | Abgeschirmt |
| Besonderheiten | Geformt, Daumenschrauben, Zugentlastung, EMI-Schutz |
| Länge | 15 cm |
| Anschluss | 15-polige HD D-Sub (HD-15) - männlich |
| Stecker (zweites Ende) | 2 x 15-polige HD D-Sub (HD-15) - weiblich |
| Bewertete Spannung | DC 300 V |
| Farbe | Schwarz |

Technische Daten © 1WorldSync. Technische Änderungen und Irrtümer vorbehalten.