

# Intellinet Network Cabinet, Free Standing (Basic)

36U - Usable Depth 123 to 773mm/Width 503mm - Black - Flatpack - Max 600kg - Server Rack - IP20 rated - 19" - Steel - Single-Point Door Lock - One Lock Per Side Panel - Three Year Warranty - Basic - Schrank Netzwerkschrank - Schwarz - RAL 9005 - 36U - 48.3 cm (19")



Gruppe	Racks
Hersteller	Intellinet
Hersteller Art. Nr.	715447
EAN/UPC	0766623715447

## Beschreibung

Intellinet Network Cabinet, Free Standing (Basic), 36U, Usable Depth 123 to 773mm/Width 503mm, Black, Flatpack, Max 600kg, Server Rack, IP20 rated, 19", Steel, Single-Point Door Lock, One Lock Per Side Panel, Three Year Warranty - Basic - Schrank Netzwerkschrank - Schwarz, RAL 9005 - 36U - 48.3 cm (19")

## Hauptmerkmale

Produktbeschreibung	Intellinet Network Cabinet, Free Standing (Basic), 36U, Usable Depth 123 to 773mm/Width 503mm, Black, Flatpack, Max 600kg, Server Rack, IP20 rated, 19", Steel, Single-Point Door Lock, One Lock Per Side Panel, Three Year Warranty - Basic - Schrank - 36U
Produkttyp	Schrank
Regaltyp	Netzwerkschrank
Packungsinhalt	Perforierte vordere Tür, perforierte hintere Tür, Glasfronttür, Montageschienen, Seitenelement, Rückwand, 4 einstellbare Stützfüße, 4 tiefenverstellbare Montageschienen, Kabeleingang
Farbe	Schwarz, RAL 9005
Rack-Größe	48.3 cm (19")
Höhe (Rack-Einheiten)	36U
Produktmaterial	Verzinktes Metall
Abmessungen (Breite x Tiefe x Höhe)	60 cm x 100 cm x 176.6 cm
Gewicht	104.9 kg
Funktionen	Abnehmbare Seitenteile, perforierte Fronttür (65 %), perforierte Hintertür (65 %), Mehrfachverriegelung

Technische Daten © 1WorldSync. Technische Änderungen und Irrtümer vorbehalten.