

Manhattan USB-C to VGA and USB-C (inc Power Delivery), 1080p@60Hz, 19.5cm, Black, Power Delivery to USB-C Port (60W)



Equivalent to Startech CDP2VGAUCP - Male to Female - Lifetime Warranty - Retail Box - Videoadapter - 24 pin USB-C (M) zu HD-15 (VGA) (W) - USB 3.2 Gen 1 / Thunderbolt 3 - 3 A - 19.5 cm - geformt - 1080p-Unterstützung - USB Power Delivery (60W) - Schwarz

Gruppe	Kabel / Adapter
Hersteller	Manhattan
Hersteller Art. Nr.	153430
EAN/UPC	0766623153430

Beschreibung

Manhattan USB-C to VGA and USB-C (inc Power Delivery), 1080p@60Hz, 19.5cm, Black, Power Delivery to USB-C Port (60W), Equivalent to Startech CDP2VGAUCP, Male to Female, Lifetime Warranty, Retail Box - Videoadapter - 24 pin USB-C (M) zu HD-15 (VGA) (W) - USB 3.2 Gen 1 / Thunderbolt 3 - 3 A - 19.5 cm - geformt, 1080p-Unterstützung, USB Power Delivery (60W) - Schwarz

Hauptmerkmale

Produktbeschreibung	Manhattan USB-C to VGA and USB-C (inc Power Delivery), 1080p@60Hz, 19.5cm, Black, Power Delivery to USB-C Port (60W), Equivalent to Startech CDP2VGAUCP, Male to Female, Lifetime Warranty, Retail Box - Videoadapter - 24 pin USB-C zu HD-15 (VGA) - 19.5 cm
Typ	Videoadapter
Technologie	Abgeschirmt
Besonderheiten	Geformt, 1080p-Unterstützung, USB Power Delivery (60W), Zugentlastung, ABS-Steckergehäuse
Länge	19.5 cm
Anschluss	24 pin USB-C - männlich
Stecker (zweites Ende)	15-polige HD D-Sub (HD-15) - weiblich
Bewertete Stromstärke	3 A
Produktzertifizierungen	USB 3.2 Gen 1 / Thunderbolt 3
Farbe	Schwarz

Technische Daten © 1WorldSync. Technische Änderungen und Irrtümer vorbehalten.