

SanDisk Extreme[®] for Action Cameras microSD[™] UHS-I Card with Adapter Europe/Asia-Pacific/Latin America/Middle East & Africa Set-up Sheet

Specifications

- Up to 100MB/s (667X) read speed, up to 90MB/s write**
- 4K UHD and Full HD Video¹
- Class 10, App Performance Class 1 (A1)²
 Video Speed Class 30 (V30)³,
 UHS Speed Class 3 (U3)³
- RescuePRO® Deluxe one year media recovery software (download offer)⁴
- SD adapter included
- Lifetime warranty⁵





Capacities	Performance		
128GB*	C10, U3, V30, A1		
Up to	100MB/s read; 90MB/s write**		
32GB-64GB	C10, U3, V30, A1		
Up to	100MB/s read: 60MB/s write		









Set-up information: 32GB, 64GB and 128GB*

Product Name	Sales Item No.	Single Pack UPC	Master Carton UPC (SCC-14)
32GB SanDisk Extreme® microSDHC™ UHS-I Card with adapter	SDSQXAF-032G-GN6AA	619659155100	6 06 19659 15510 2
64GB SanDisk Extreme® microSDXC™ UHS-I Card with adapter	SDSQXAF-064G-GN6AA	619659155964	6 06 19659 15596 6
128GB SanDisk Extreme® microSDXC™ UHS-I Card with adapter	SDSQXAF-128G-GN6AA	619659156046	60619659156048

Dimensions: 32GB, 64GB and 128GB*

	Weight	Dimensions (H x W x L)	Other
Individual Product (card)	0.01 lb. 4.54 g	0.43 × 0.59 × 0.04 in. 10.92 × 14.99 × 1.02 mm	
Individual Product (adapter)	0.01 lb. 4.54 g	1.25 x 0.94 x 0.08 in. 31.75 x 23.88 x 2.03 mm	 Master Carton Qty: 25 Languages on Package: English, French, Italian, German, Spanish, Russian Country of Origin: China or Taiwan Warranty: Lifetime warranty⁵ Has main plug: N/A Batteries required: N/A Batteries included: N/A Battery weight: N/A
Single Package	0.03 lb. 14.30 g	6.00 x 4.00 x 0.26 in. 152.40 x 101.60 x 6.62 mm	
Packaging Paper	8 g		
Packaging Tray	1.70 g		
Total Packaging w/o product	9.70 g		Battery material: N/A Battery capacity: N/A
Master Package	0.97 lb. 440.51 g	6.25 x 4.13 x 3.13 in. 158.75 x 104.90 x 79.50 mm	Battery life: N/A

☑ Water Proof⁶

☑ Temperature Proof⁶

☑ Shock Proof⁶

☑ X-Ray Proof⁶









- 1GB=1.000.000.000 bytes. Actual user storage less.
- 32GB-64GB: Up to 100MB/s (667X) read; up to 60MB/s (400X) write. Based on internal testing; performance may be lower depending on host device. 1MB = 1,000,000 bytes
- ** **128GB:** Up to 100MB/s (667X) read; up to 90MB/s (600X) write. Based on internal testing; performance may be lower depending on host device. 1MB = 1,000,000 bytes
- Compatible device required. 4K UHD (3840x2160) video support may vary based upon host device, file attributes, and other factors. See www.sandisk.com/HD
- Results may vary based on host device, app type and other factors
- 3 32GB-128GB: Video Speed Class 30 (V30), sustained video capture rate of 30MB/s, and UHS Speed Class 3 (U3) designate a performance option designed to support real-time video recording with UHS enabled host devices. See www.sdcard.org/consumers/speed
- Registration required. Terms and conditions apply
- 5 See www.sandisk.com/wug
- 6 Card only: See www.sandisk.com/proof

SanDisk, RescuePRO and SanDisk Extreme are registered trademarks or trademarks of Western Digital Corporation or its affiliates in the US and/or other countries. The microSD, microSDHC, microSDXC, SDHC and SDXC marks and logos are trademarks of SD-3C, LLC. Android is a trademark of Google Inc. The Android robot is reproduced or modified from work created and shared by Google and used according to terms described in the Creative Commons 3.0 Attribution License. Windows and the Windows logo are trademarks of the Microsoft group of companies. All other marks are the property of their respective owners. © 2017 Western Digital Corporation. All rights reserved. Rev. 4/17

Western Digital Technologies, Inc. is the seller of record and licensee in the Americas of SanDisk® products.