

# Manhattan Stereo Over-Ear Headset (3.5mm), Microphone Boom (padded)

Adjustable Steel Headband - In-Line Volume Control - Ear Cushions - Std 2x 3.5mm stereo jack/plug for audio/mic use - cable 2.5m - 3 Year Warranty - Headset - On-Ear - kabelgebunden - 3,5 mm Stecker



Gruppe	Audio Ein-/Ausgabegeräte
Hersteller	Manhattan
Hersteller Art. Nr.	175555
EAN/UPC	0766623175555

## Beschreibung

Manhattan Stereo Over-Ear Headset (3.5mm), Microphone Boom (padded), Adjustable Steel Headband, In-Line Volume Control, Ear Cushions, Std 2x 3.5mm stereo jack/plug for audio/mic use, cable 2.5m, 3 Year Warranty - Headset - On-Ear - kabelgebunden - 3,5 mm Stecker

## Hauptmerkmale

Produktbeschreibung	Manhattan Stereo Over-Ear Headset (3.5mm), Microphone Boom (padded), Adjustable Steel Headband, In-Line Volume Control, Ear Cushions, Std 2x 3.5mm stereo jack/plug for audio/mic use, cable 2.5m, 3 Year Warranty - Headset
Produkttyp	Headset - kabelgebunden - 3,5 mm Stecker
Empfohlene Verwendung	Computer
Kopfhörer-Formfaktor	On-Ear
Anschlussstechnik	Kabelgebunden
Soundmodus	Stereo
Audiospezifikationen	Frequenzbereich 20 - 20000 Hz - Empfindlichkeit 105 dB
Impedanz	32 Ohm
Mikrofon	Mikrofonbaum
Mikrofontechnologie	Elektret-Kondensator
Betriebsart des Mikrofons	Ungerichtet

Technische Daten © 1WorldSync. Technische Änderungen und Irrtümer vorbehalten.