

# Manhattan USB-A to SATA/IDE Adapter Cable, 3-in-1 with One-Touch Backup, Male to Male, 1.5m, 480 Mbps (USB 2.0)

Hi-Speed USB - Black - Three Year Warranty - Blister - Speicher-Controller - 2.5" - 3.5" - 5.25" (6.4 cm - 8.9 cm - 13.3 cm) - ATA-100 / SATA 1.5Gb/s - USB 2.0



Gruppe	Kabel / Adapter
Hersteller	Manhattan
Hersteller Art. Nr.	179195
EAN/UPC	0766623179195

## Beschreibung

Manhattan USB-A to SATA/IDE Adapter Cable, 3-in-1 with One-Touch Backup, Male to Male, 1.5m, 480 Mbps (USB 2.0), Hi-Speed USB, Black, Three Year Warranty, Blister - Speicher-Controller - 2.5", 3.5", 5.25" (6.4 cm, 8.9 cm, 13.3 cm) - ATA-100 / SATA 1.5Gb/s - USB 2.0

## Hauptmerkmale

Produktbeschreibung	Manhattan USB-A to SATA/IDE Adapter Cable, 3-in-1 with One-Touch Backup, Male to Male, 1.5m, 480 Mbps (USB 2.0), Hi-Speed USB, Black, Three Year Warranty, Blister - Speicher-Controller - ATA-100 / SATA 1.5Gb/s - USB 2.0
Gerätetyp	Speicher-Controller - extern
Bustyp	USB 2.0
Kompatibilität mit Festplattenlaufwerk-Formfaktor	2.5", 3.5", 5.25" (6.4 cm, 8.9 cm, 13.3 cm)
Schnittstelle	ATA-100 / SATA 1.5Gb/s
Unterstützte Geräte	Festplatte, CD Laufwerk, DVD-Laufwerk
Stromversorgung	Wechselstrom 120/230 V (50/60 Hz)
Systemanforderungen	Linux, Apple MacOS 9.x, Apple MacOS X 10.x, Microsoft Windows XP / Vista / 7 / 8 / 8.1 / 10
Abmessungen (Breite x Tiefe x Höhe)	9.8 cm x 7 cm x 1.8 cm
Gewicht	270 g

Technische Daten © 1WorldSync. Technische Änderungen und Irrtümer vorbehalten.