





Outstanding transfer performance

Transcend's CompactFlash 800 cards operate in Ultra DMA (UDMA) transfer mode 7, the fastest interface speed available for CF cards. A mid-range DSLR camera equipped with a 800x CF card can respond more quickly during fast-action burst mode shooting, and store large images in RAW format faster than ever before.



Video Performance Guarantee

The Video Performance Guarantee (VPG-20) of the CompactFlash 800 cards guarantees constant video recording at 20MB/s without dropping frames. As the class-leading storage for ultra-high resolution Full HD and 3D video recording, the CompactFlash 800 cards deliver smooth, professional video recording quality.



Excellent compatibility

Transcend's CompactFlash 800 cards are developed to work across a wide range of CompactFlash compatible devices, including mid-range DSLRs, hybrid cameras and Full HD camcorders. When paired with a high-end card reader such as Transcend's USB 3.1 Gen 1 RDF8, the CompactFlash 800 cards can achieve optimum read/write speed and provide seamless data transfer.





CompactFlash Cards

CompactFlash 800

Features

- Supports high-speed Ultra DMA transfer mode 7
- Video Performance Guarantee (VPG-20)
- · Up to 256GB storage capacity
- · Up to 120 MB/s read; 60 MB/s write
- · MLC NAND flash memory
- Ideal for ultra-high resolution Full HD and 3D video recording
- · Exclusive RecoveRx software



RecoveRx software

Transcend offers RecoveRx software, a data recovery utility that allows you to search deep within a storage device for traces of erased files including digital photos, documents, music and videos.

Specifications

Α	n	n	\cap	1	\mathbf{r}	1	\mathbf{n}	-	\cap
$\overline{}$	IJ	IJ	\subset	α		а	11	L	\Box

Dimensions (Max.)	42.8 mm x 36.4 mm x 3.3 mm (1.69" x 1.43" x 0.13")
Weight (Max.)	11.4 g (0.4 oz)
Storage	
Flash Type	MLC NAND flash

32 GB/64 GB/128 GB/256 GB

Operating Environment

Operating Temperature	-25°C (-13°F) ~ 85°C (185°F)
Operating Voltage	3.3V ~ 5V

Performance

Capacity

Read Speed (Max.)	120 MB/s
Write Speed (Max.)	60 MB/s
Insertion/Removal Cycles	10,000

Note

Speed may vary due to host hardware, software, usage, and storage capacity.

Warranty

Certificate	CE/FCC/RCM/EAC
Warranty	Five-year Limited Warranty

Ordering Information

32GB	TS32GCF800
64GB	TS64GCF800
128GB	TS128GCF800
256GB	TS256GCF800