

# Intel Core i5 13500 - 2.5 GHz - 14 Kerne - 20 Threads

24 MB Cache-Speicher - FCLGA1700 Socket - Box

Gruppe	Prozessoren
Hersteller	Intel
Hersteller Art. Nr.	BX8071513500
EAN/UPC	5032037260251



## Beschreibung

Intel Core i5 13500 - 2.5 GHz - 14 Kerne - 20 Threads - 24 MB Cache-Speicher - FCLGA1700 Socket - Box

## Hauptmerkmale

Produktbeschreibung	Intel Core i5 13500 / 2.5 GHz Prozessor - Box
Produkttyp	Prozessor
Prozessortyp	Intel Core i5 13500 (13th Gen)
Anz. der Kerne	14 Kerne / 20 Threads
Cache-Speicher	24 MB
Integrierte Grafik	Intel UHD Graphics 770
Geeignete Sockel	FCLGA1700 Socket
Prozessoranz.	1
Taktfrequenz	2.5 GHz (P-Kern) / 1.8 GHz (E-Kern)
Max. Turbo-Taktfrequenz	4.8 GHz (P-Kern) / 3.5 GHz (E-Kern)
Funktionen	Enhanced SpeedStep technology, Hyper-Threading-Technologie, Unterstützung für Execute Disable Bit, Intel Virtualization Technology, Intel 64 Technology, Intel Trusted Execution Technology, Intel Turbo Boost Technology 2.0, Intel AES New Instructions (AES-NI), Thermal Monitoring Technologies, Intel Virtualization Technology for Directed I/O (VT-d), Idle States, Intel VT-x with Extended Page Tables (EPT), Intel Secure Key, Intel OS Guard, Intel Turbo Boost Max Technology 3.0, Intel Speed Shift Technology, Intel Volume Management Device (VMD), Intel Boot Guard, Intel Deep Learning Boost (DL Boost), Intel Control-Flow Enforcement Technology, Intel Gaussian and Neural Accelerator 3.0, Intel Thread Director, Instruction Set 64-bit, Intel Standard Manageability (ISM), Intel Virtualization Technology with Redirect Protection (VT-rp), Mode-based Execute Control (MBEC)

Technische Daten © 1WorldSync. Technische Änderungen und Irrtümer vorbehalten.