

Intel Celeron G6900 - 3.4 GHz - 2 Kerne - 2 Threads

4 MB Cache-Speicher - LGA1700 Socket - Box

Gruppe	Prozessoren
Hersteller	Intel
Hersteller Art. Nr.	BX80715G6900
EAN/UPC	5032037238755



Beschreibung

Intel Celeron G6900 - 3.4 GHz - 2 Kerne - 2 Threads - 4 MB Cache-Speicher - LGA1700 Socket - Box

Hauptmerkmale

Produktbeschreibung	Intel Celeron G6900 / 3.4 GHz Prozessor - Box
Produkttyp	Prozessor
Prozessortyp	Intel Celeron G6900
Anz. der Kerne	Dual-Core / 2 Threads
Cache-Speicher	4 MB
Integrierte Grafik	Intel UHD Graphics 710
Geeignete Sockel	LGA1700 Socket
Prozessoranz.	1
Taktfrequenz	3.4 GHz
Herstellungsprozess	10 nm
Funktionen	Enhanced SpeedStep technology, Unterstützung für Execute Disable Bit, Intel Virtualization Technology, Intel 64 Technology, Streaming-SIMD-Erweiterungen 4.1, Streaming-SIMD-Erweiterungen 4.2, Intel AES New Instructions (AES-NI), Thermal Monitoring Technologies, Intel Virtualization Technology for Directed I/O (VT-d), Idle States, Intel VT-x with Extended Page Tables (EPT), Intel Secure Key, Intel Advanced Vector Extensions 2 (AVX2.0), Intel OS Guard, Intel Speed Shift Technology, Intel Optane Memory Supported, Mode-based Execute Control (MBE), Intel Volume Management Device (VMD), Intel Boot Guard, Intel Deep Learning Boost (DL Boost), Intel Control-Flow Enforcement Technology, Intel Gaussian and Neural Accelerator 3.0, Instruction Set 64-bit

Technische Daten © 1WorldSync. Technische Änderungen und Irrtümer vorbehalten.