

850 W / 750 W / 650 W / 550 W



SPECIAL FEATURES

- ❖ High Efficiency, 80 PLUS® Bronze Certified
- ❖ Compact ATX Size [140 mm deep]
- ❖ Smart and Silent Fan Control
- ❖ Tight Voltage Regulation (12 V, 5 V, 3.3 V) [± 3 %]
- ❖ Ample +12 V Output
- ❖ 5 Years Warranty

POWER DISTRIBUTION

Model	+3.3 V	+5 V	+12 V	-12 V	+5 Vsb	Total Power
B12 BC-850	15 A	15 A	70 A	0.3 A	2.5 A	850 W
		100 W	840 W	3.6 W	12.5 W	
B12 BC-750	15 A	15 A	62 A	0.3 A	2.5 A	750 W
		100 W	744 W	3.6 W	12.5 W	
B12 BC-650	15 A	15 A	54 A	0.3 A	2.5 A	650 W
		100 W	648 W	3.6 W	12.5 W	
B12 BC-550	15 A	15 A	45 A	0.3 A	2.5 A	550 W
		100 W	540 W	3.6 W	12.5 W	

CONNECTOR QUANTITY

Connector					
Model	Main Power (24P / 20P) 550 mm	EPS 12 V / ATX 12 V (8P / 4P) 600 mm	PCI-E (8P / 6P)	SATA	Peripheral (4P)
B12 BC-850	1	2	4	6	3
B12 BC-750	1	2	4	6	3
B12 BC-650	1	1	4	6	3
B12 BC-550	1	1	2	6	3

Safety & EMI / EMC



Protection Features: OPP / OVP / SCP / UVP

Dimensions: 150 mm (L) x 140 mm (W) x 86 mm (H)



Specifications may change without prior notice



Headquarters sales@seasonic.com
 USA ssa.sales@seasonic.com
 Europe sse.sales@seasonic.com

www.seasonic.com