

Set your creativity free









da Vinci Jr.

# **XYZprinting**

# da Vinci Jr.

### Lightweight Printer with Large Build Volume

The compact and seamless printer weights only 26.46 lbs and the maximum build volume 5.9"x5.9"x5.9" inches ( $150 \times 150 \times 150$ 

#### Safety-ensured

The enclosed printing area and non-heating bed ensures a safe printing environment.

#### Stand Alone

Built-in SD card slot allows users to print from SD card directly.

#### **Easy Loading**

Adopting NFC technology makes filament detecting and replacing easy.



#### **Eco-Friendly**

The system consumes only as low as 75W of power for printing and supports PLA material, which is the most highly efficient biodegradable plastics.



#### **Cloud Database**

XYZprinting's design gallery is a public cloud database with thousands of 3D models for downloading. The gallery is also open for uploading users' designs.

## PLA Refillable Filament

Cartridge recycle saves your money and leads to friendly environment. Smart locker design makes spool refill as easy as a breeze.





ua viiici jr.5peiiicai	
Dimension w/ Spool (WxHxD)	16.54 x 14.96 x 16.93 inches (420 x 430 x 380 mm)
Net Weight (Cartridges included)	26.46 lbs (12kg)
Panel Type	2.6" FSTN LCM
Language	English / Japanese
Connectivity	USB Wire / SD Card
Technology	FFF (Fused Filament Fabrication)
Maximum Build Volume (WxHxD)	5.9 x 5.9 x 5.9 inches (15 x15x15cm)
Printing Mode	100 - 400 microns
Print Head	Single Nozzle
Nozzle Diameter	0.4 mm
Filament Diameter	1.75 mm
File Types	.stl , XYZ Format(.3w)
Software OS Supports	Windows 7 - 8 above (for PC)
	Mac OSX 10.8 64-bit above (for Mac)
Hardware Requirements	X86 32/64-bit compatible PCs with 2GB+ DRAM (for PC)
	X86 64-bit compatible Macs with 2GB+ DRAM (for Mac)

<sup>\*</sup>Specifications are subject to change without notice.

