

	-10°C ... +75°C	0°C ... +35°C	40 mm	100 ... 240 V~ 50 / 60 Hz	8 mm 1...2,5 mm ²

	R		L		C/L		Dimmable	Dimmable
240V~ 50Hz	3 ... 400 W	3 ... 400 VA	3 ... 200 VA	3 ... 400 VA	3 ... 200 VA	3 ... 75 W ≤ 10 x		
100V~ 60Hz	3 ... 200 W	3 ... 200 VA	3 ... 100 VA	3 ... 200 VA	3 ... 100 VA	3 ... 37 W ≤ 10 x		



