

SCD-100BK

Portable PLL FM Radio with CD MP3, Bluetooth, USB and SD Player



EN

- Bluetooth
- Toploading CD/MP3 player
- Programmable memory for 20 CD tracks
- PLL FM radio
- LCD display
- Clock function
- Output power: 2 x 5 Watt (RMS)
- 4 speakers system
- Telescopic antenna
- Included : Remote control
- Connections : USB, AUX, SD card reader, 3,5mm earphone jack

DE

- Bluetooth
- Toplader CD/MP3-Player
- Programmierbarer Speicher für 20 CD-Tracks
- PLL FM Radio
- LCD-Display
- Uhrfunktion
- Ausgangsleistung: 2 x 5 Watt (RMS)
- System mit 4 Lautsprechern
- Teleskopantenne
- Inklusiv: Fernbedienung
- Anschlüsse: USB, AUX, SD-Kartenleser, 3,5 mm Kopfhörerbuchse

NL

- Bluetooth
- Bovenlader voor CD/ MP3 speler
- Programmeerbaar CD geheugen voor 20 nummers
- PLL FM radio
- LCD scherm
- Klok functie
- Uitgangsvermogen : 2 x 5 Watts (RMS)
- Systeem met 4 luidsprekers
- Telescopische antenne
- Inclusief: Afstandsbediening
- Aansluitingen : USB, AUX, SD Kaartlezer, Audio uitgang 3,5 mm

FR

- Bluetooth
- Lecteur CD/MP3 à chargement par le haut
- Mémoire programmable pour 20 pistes CD
- Radio FM avec tuner PLL
- Écran LCD
- Fonction horloge
- Puissance de sortie: 2 x 5 Watts RMS
- Système à 4 haut-parleurs
- Antenne télescopique
- Inclus: Commande à distance
- Connexions : USB, AUX, Lecteur de carte SD, Prise casque de 3,5 mm

ES

- Bluetooth
- Reproductor de CD/MP3
- Memoria programable para 20 pistas
- Radio FM PLL
- Pantalla LCD
- Función reloj
- Potencia de salida: 2 x 5 Watt (RMS)
- Sistema de 4 altavoces
- Antena telescópica
- Incluye: Mando a distancia
- Conexiones: USB, AUX, Lector de tarjetas SD, Sortida para auriculares de 3.5mm

DATA

- Power source: AC 230V 50Hz
- Power consumption max/standby : 22W/ 0,8W
- Battery (for main unit) : 6 x UM2 (C size) (not included)
- Battery (for remote control) : 1 x CR2025 (included)
- Dim. unit : 372 x 273 x 160 mm (WxDxH)
- Net/Gross Weight: 2,40 kg / 3,2 kg
- Master carton quantity : 2pcs
- EAN-code: 87.11902.03949.5

Container quantity :
20' ft : 1060 pcs
40' ft : 2220 pcs
40' HQ : 2600 pcs

Subject to changes without prior notice

