

**Manhattan TV & Monitor Mount with built-in Dock/Hub, Desk, Full Motion (Gas Spring), 2 screens (to 27"), Ports (x7): Ethernet, HDMI (x2), USB-A (x3) and USB-C, Power Delivery (100W) to USB-C Port (Separate USB-C wall charger/cable needed),Dual Screen,VESA 100x100mm Befestigungskit - Voll beweglich - für 2 LCD-/Plasma-Konsolen - 8-in-1 Dockingstation - Schwarz**



Produktbeschreibung: Manhattan TV & Monitor Mount with built-in Dock/Hub, Desk, Full Motion (Gas Spring), 2 screens (to 27"), Ports (x7): Ethernet, HDMI (x2), USB-A (x3) and USB-C, Power Delivery (100W) to USB-C Port (Separate USB-C wall charger/cable needed),Dual Screen,VESA 100x100mm - Befestigungskit (Dual-Schwenkarm, Gasfeder) - Voll beweglich - für 2 LCD-/Plasma-Konsolen - 8-in-1 Dockingstation - Aluminium - Schwarz - Bildschirmgröße: 43.2-81.3 cm (17"-32") - Tischmontage

Gruppe: AV-Möbel  
 Hersteller: IC Intracom  
 Hersteller Artikel Nr: 461887  
 EAN: 0766623461887

Hauptmerkmale	
Produktbeschreibung	Manhattan TV & Monitor Mount with built-in Dock/Hub, Desk, Full Motion (Gas Spring), 2 screens (to 27"), Ports (x7): Ethernet, HDMI (x2), USB-A (x3) and USB-C, Power Delivery (100W) to USB-C Port (Separate USB-C wall charger/cable needed),Dual Screen,VESA 100x100mm Befestigungskit - Voll beweglich - für 2 LCD-/Plasma-Konsolen - 8-in-1 Dockingstation - Schwarz
Produkttyp	Befestigungskit (Voll beweglich) - Tischmontage
Montagekomponenten	Dual-Schwenkarm, Gasfeder
Integrierte Geräte	Dockingstation (RJ-45 / 2 x HDMI / 2 x USB-C / 3 x USB-A)
Abmessungen (Breite x Tiefe x Höhe)	11.5 cm x 101.8 cm x 56 cm
Neigung	-45 ° bis 45 °
Rotation	360°
Drehen	180°
Anpassungen	Höhe, Neigung
Gewicht	4.55 kg
Empfohlene Verwendung	2 LCD-/Plasma-Konsolen
Empfohlene Display-Größe	43.2-81.3 cm (17"-32")
VESA-Halterung	100 x 100 mm, 75 x 75 mm

Max. Ladegewicht	9 kg
Material	Aluminium
Farbe	Schwarz
Packungsinhalt	Befestigungsset für Montage, Kabel USB-C auf USB-C (1 m)