



Manhattan M.2 NVMe and SATA SSD Enclosure, USB-C & USB-A Male Connection, Up to 10 Gbps (USB 3.2 Gen2 aka USB 3.1), For 2230/2242/2260/2280 SSDs with M Key or B+M Key, SuperSpeed+ USB, Aluminum, Black, Three Year Warranty, Box - Speichergehäuse - M.2 - M.2 NVMe Card / SATA 10Gb/s - USB 3.2 (Gen 2), Thunderbolt 3 - Schwarz

Produktbeschreibung	Manhattan M.2 NVMe and SATA SSD Enclosure, USB-C & USB-A Male Connection, Up to 10 Gbps (USB 3.2 Gen2 aka USB 3.1), For 2230/2242/2260/2280 SSDs with M Key or B+M Key, SuperSpeed+ USB, Aluminum, Black, Three Year Warranty, Box - Speichergehäuse - M.2 NVMe Card / SATA 10Gb/s - USB 3.2 (Gen 2), Thunderbolt 3
Gerätetyp	Speichergehäuse - extern
Bustyp	USB 3.2 (Gen 2), Thunderbolt 3
Farbe	Schwarz
Erweiterungseinschübe	1 x intern - M.2 2242/2260/2280
Kompatibilität mit Festplattenlaufwerk-Formfaktor	M.2
Schnittstelle	M.2 NVMe Card / SATA 10Gb/s
Datenübertragungsrate	10 Gbit/s
Unterstützte Geräte	Solid State-Laufwerk
Max. Anzahl Speicherperipheriegeräte	1
Verpackung	Retail
Produktmaterial	Aluminium
Stromversorgung	USB-Bus
Systemanforderungen	Linux, Android, Microsoft Windows 7 oder höher, Apple MacOS



Abmessungen (Breite x Tiefe x Höhe)	3.1 cm x 14 cm x 0.9 cm
Gewicht	45 g

Technische Daten © 1WorldSync. Technische Änderungen und Irrtümer vorbehalten.